


## Multimeter Accessories for Electronic Applications



### TL910 Electronic Test Probes with Replacement Tips



- Small profile design is comfortable and allows accessibility to hard to reach test points
- Comes with 5 sets of replaceable tips (Includes 3 sets of spring loaded gold plated and 2 sets of stainless steel replacement tips)
- Probes are 102 mm (4") long and include 1 m (39") leads
- Compatible with all instruments that accept standard 4 mm (.160"), shrouded banana plugs
- CAT IV, 600V; CAT III, 1000V, 3A
- Replacement tips available as Fluke model TP912
- One year warranty

### TP912 Replacement Tips for Electronic Test Probes (TL910)

- Includes five sets of sharp, 0.040" diameter replacement tips:
  - 2 ea - 25 mm (1") long stainless steel
  - 2 ea - 102 mm (4") long stainless steel
  - 2 ea - Gold-plated, spring loaded, single point plunger
  - 2 ea - Gold-plated, spring loaded, 3-point plunger
  - 2 ea - Gold plated, spring loaded, 4-point plunger
- One year warranty

### TP920 Test Probe Adapter Kit

- Kit includes push-on adapters for test probes
- Recommended for use with Fluke TL71 and TL75 Test Lead Sets
- IC Test Tip adapters for probing closely spaced test points such as integrated circuit leads without shorting adjacent leads. Maximum 3A
- Extended Probe Tips allow testing of hard to reach points. Maximum 3A
- Medium Alligator Clips have maximum jaw opening of 0.76 mm (0.30"). Maximum 5A
- CAT II, 300V, maximum amps (as noted)
- One year warranty



### Fluke TL930 61 cm (24") and TL932 91 cm (36") Patch Cords


- 1 pair (red and black) multi-stacking 4 mm banana plug patch cords
- PVC insulated leads
- Nickel-plated banana plugs
- Maximum ratings for non-hazardous applications 5000V, <1/2 mA
- Maximum ratings for CE compliance 30 Vrms or 60 Vdc, 15 Amps
- One year warranty

### Fluke TL935 Patch Cord Kit

- Kit includes 3 sets (red and black pairs) multi-stacking 4 mm banana plug patch cords
- 61 cm (24"), 91 cm (36"), 122 cm (48") long PVC insulated leads
- Nickel-plated banana plugs
- Maximum ratings for non-hazardous applications 5000V, <1/2 mA
- Maximum ratings for CE compliance 30 Vrms or 60 Vdc, 15 Amps
- One year warranty

### Fluke TL940 Mini-Hook Test Leads

- 1 pair (red and black) test leads with multi-stacking 4 mm banana plugs and mini-hooks
- Mini-hooks attach to component leads up to 1.5 mm (0.060") diameter
- 91 cm (36") long PVC insulated leads
- Maximum ratings for non-hazardous applications 300V, <1/2 mA
- Maximum ratings for CE compliance 30 Vrms or 60 Vdc, 15 amps
- One year warranty




## Fluke TL950 Mini-Pincer Test Leads

- 1 pair (red and black) test leads with multi-stacking 4 mm banana plugs and mini-pincers
- Mini-pincers open to 2.3 mm (0.090")
- 91 cm (36") long PVC insulated leads
- Maximum ratings for non-hazardous applications 300V, <1/2 mA
- Maximum ratings for CE compliance 30 Vrms or 60 Vdc, 15 amps
- One year warranty



## Fluke TL960 Micro-Hook Test Leads


- 1 pair (red and black) test leads with multi-stacking 4 mm banana plugs and micro-hooks
- Micro-hooks attach to component leads up to 1 mm (0.040") diameter
- 91 cm (36") long PVC insulated leads
- Maximum ratings for non-hazardous applications 150V, <1/2 mA
- Maximum ratings for CE compliance 30 Vrms or 60 Vdc, 15 amps
- One year warranty



## Fluke TL970 Hook and Pincer Kit

Handy all-in-one kit that includes 3 pairs (red and black) test leads:

- Multi-stacking 4 mm banana plugs to mini-hooks which attach to component leads up to 1.5 mm (0.060") in diameter
  - Maximum ratings for non hazardous applications 300V, <1/2 mA
  - Maximum ratings for CE compliance 30 Vrms or 60 Vdc, 5 amps
- Multi-stacking 4 mm banana plugs to mini-pincers which open to 2.3 mm (0.090")
  - Maximum ratings for non hazardous applications 300V, <1/2 mA
  - Maximum ratings for CE compliance 30 Vrms or 60 Vdc, 5 amps
- Multi-stacking 4 mm banana plugs to micro-hooks which attach to component leads up to 1 mm (0.040") in diameter
  - Maximum ratings for non hazardous applications 150V, <1/2 mA
  - Maximum ratings for CE compliance 30 Vrms or 60 Vdc, 3 amps
- All have 91 cm (36") long PVC insulated leads
- One year warranty



## Fluke BP980 Double Banana Plug Kit

- Kit includes 5 pair (red and black) of double 4 mm banana plugs
- Each banana plug has 3.1 mm (0.125") diameter holes for mounting wires and components with set screws
- Each banana plug has nickel-plated brass plugs/, jacks beryllium copper springs
- Molded with durable ABC insulation
- Maximum ratings for non-hazardous applications 5000V, <1/2 mA
- Maximum ratings for CD compliance 30 Vrms or 60 Vdc, 15 Amps
- One year warranty



## Fluke H900 Test Lead Holder

- Heavy duty test lead holder
- Durable powder coat finish in distinctive Fluke colors
- Holder has 10 slots for wires up to 8.1 mm (0.32") in diameter
- Comes with mounting holes for convenient installation
- Over all dimensions: 27.9 cm L x 8.9 cm W x 3.2 cm H (11" L x 3.5" W x 1.25" H)
- One year warranty

**Fluke.** Keeping your world up and running.

### Fluke Corporation

PO Box 9090, Everett, WA USA 98206

Fluke Europe B.V.

PO Box 1186, 5602 BD

Eindhoven, The Netherlands

For more information call:

U.S.A. (800) 443-5853 or Fax (425) 446-5116

Europe/M-East/Africa (31 40) 2 675 200 or

Fax (31 40) 2 675 222

Canada (800) 36-FLUKE or Fax (905) 890-6866

Other countries (425) 446-5500 or

Fax (425) 446-5116

Web access: <http://www.fluke.com>

©2001 Fluke Corporation. All rights reserved.

Trademarks are the property of their respective owners.

Printed in U.S.A. 8/2001 1628503 D-ENG-N Rev A