


Enhance your power with these current transformers

Technical Data

Fluke Power Quality Current Transformers are specially designed to work seamlessly with Fluke Power Quality / RPM Full Disclosure™ Power Monitors. All Clamp-on and Flexi-CT's are matched to take full advantage of your instrument's ability to set scale factors for accurate readings.



Clamp-on Current Transformers

Model No.	CT Type	Current Range	Accuracy	Frequency Response	Jaw Opening
3005R	Clamp-On	0.01-5A	1 % RDG +/- 0.5 % FS	5 kHz	.78" dia. (2 cm)
3014	Clamp-On	0.1-40A	1 % RDG +/- 0.1 % FS	5 kHz	.78" dia. (2 cm)
3120R	Clamp-On	0.5-200A	1 % RDG +/- 0.3 % FS	5 kHz	.78" dia. (2 cm)
3100R	Clamp-On	1-1000A	1 % RDG +/- 0.05 % FS	5 kHz	2" dia. (5 cm)
3300	Clamp-On	10-3000A	2 % RDG +/- 0.05 % FS	5 kHz	3.5 x 4.5" (9 x 11 cm)



Flexi-CT™ Flexible Current Transformers

Model No.	CT Type	Current Range	Accuracy	Frequency Response	Jaw Opening
3110/RPM	Flexi-CT	2-100A	1 % RDG +/- 0.5 % FS	7 kHz	24" length (0.6 cm)
3112/RPM	Flexi-CT	2-100A	1 % RDG +/- 0.5 % FS	7 kHz	48" length (1.2 cm)
3210/RPM	Flexi-CT	20-1000A	1 % RDG +/- 0.15 % FS	7 kHz	24" length (0.6 cm)
3212/RPM	Flexi-CT	20-1000A	1 % RDG +/- 0.15 % FS	7 kHz	48" length (1.2 cm)
3310/RPM	Flexi-CT	100-5000A	1 % RDG +/- 0.15 % FS	7 kHz	24" length (0.6 cm)
3312/RPM	Flexi-CT	100-5000A	1 % RDG +/- 0.15 % FS	7 kHz	48" length (1.2 cm)



Split-Core Current Transformers

Model No.	CT Type	Current Range	Accuracy	Frequency Response	Jaw Opening
3583R	Split-Core CT	0.01 - 10A	1 % RDG +/- 0.5 % FS	5 kHz	7/16" (1 cm)
3584R	Split-Core CT	0.1 - 40A	1 % RDG +/- 0.5 % FS	5 kHz	7/16" (1 cm)
3585R	Split-Core CT	0.5 - 100A	1 % RDG +/- 0.5 % FS	5 kHz	7/16" (1 cm)

Interface and Extension Cables

3570/RPM	CT Cable	Connects clamp on style CT to Power Recorder	10 feet (2.5 m)
3533/RPM	Pod Adapter	Connects Flexible CT to Hostile Enclosure Current Pod	

Fluke. *Keeping your world up and running.*

Fluke Corporation
PO Box 9090, Everett, WA USA 98206

Fluke Europe B.V.
PO Box 1186, 5602 BD
Eindhoven, The Netherlands

For more information call:
In the U.S.A. (800) 443-5853 or
Fax (425) 446-5116
In Europe/M-East/Africa (31 40) 2 675 200 or
Fax (31 40) 2 675 222
In Canada (800) 36-FLUKE or
Fax (905) 890-6866
From other countries (425) 446-5500 or
Fax (425) 446-5116
Web access: <http://www.fluke.com>