

VoltAlert™ Test voltage with easy-to-use detectors



Electricians, maintenance, service, safety personnel and homeowners can quickly test for energized circuits and defective grounds on the factory floor, in the shop or at home.

VoltAlert ac voltage testers from Fluke are easy to use – just touch the tip to a terminal strip, outlet or cord. When it glows red, you know there is voltage in the line.

- Detects voltage from 90 V ac to 600 V ac or 200 V ac to 600 V ac (requirements vary by country)
- Fits in a shirt pocket for convenience
- All outer surfaces are non-conductive for safety
- Detects voltage without metallic contact
- Manufactured in the U.S.



Specifications:

Features	
Operating ranges	Model A: 90 to 600 V ac (found in Fluke 1AC-A1-5PK) Model E: 200 to 600 V ac (found in Fluke 1AC-E-5PK)
Operating temperature	-10 °C to 50 °C (14 °F to 122 °F)
Humidity	0 °C to 30 °C, 95 % (32 °F to 86 °F) 30 °C to 40 °C, 75 % (86 °F to 104 °F) 40 °C to 50 °C, 45 % (104 °F to 122 °F)
Operating altitude	3000 m (10,000 ft.)
Enclosure	IEC 529, IP54
Weight	60.6 grams with batteries
Dimensions	146 mm long x 19 mm diameter (5.75" x 0.74")
Outer surface	Probe is composed of injection molded, high impact, non-flammable PVC and ABS
Warranty	One year



Buy
Multi Pack
and **Save**



**Buy 4
get 1 FREE**

Fluke. Keeping your world up and running.

Fluke Corporation
PO Box 9090, Everett, WA USA 98206

Fluke Europe B.V.
PO Box 1186, 5602 BD
Eindhoven, The Netherlands

For more information call:
In the U.S.A. (800) 443-5853 or
Fax (425) 446-5116
In Europe/M-East/Africa (31 40) 2 675 200 or
Fax (31 40) 2 675 222
In Canada (800)-36-FLUKE or
Fax (905) 890-6866
From other countries +1 (425) 446-5500 or
Fax +1 (425) 446-5116
Web access: <http://www.fluke.com>