

Buy a
Combo Kit
and Save over
\$50* (U.S.)



Created for industrial, HVAC and facility maintenance.

Rugged true-rms multimeter with a built-in thermometer to troubleshoot electrical and electromechanical problems plus a laser guided, non-contact infrared thermometer for measuring rotating or energized equipment. Includes test leads, temperature probe and a durable carrying case.

Ordering Information

Fluke 179/61 Kit

New

Industrial Multimeter and Infrared Thermometer Combo Kit

Fluke 179 True-rms Digital Multimeter with Temperature

- True-rms voltage and current in a rugged package
- 1000 V ac and dc ranges
- Larger, easy-to-read display
- 0.09 % accuracy. 3 times better than the original Fluke 70 Series
- Backlight for use in dark areas
- Current measurements to 10 A, 20 A for 30 sec.
- Resistance and continuity
- Frequency and capacitance
- Min/Max to capture intermittent readings
- Built in thermometer – probe included
- Attach to steel surfaces with optional TPAK magnetic hanging kit

- 1000 V CAT III electrical safety rating
- Limited lifetime warranty

Fluke 61 Infrared Thermometer

- Safely measure temperature on rotating or energized equipment
- Bright laser beam provides easy targeting
- Simple to use
- Shock-absorbing holster increases ruggedness
- Celsius or Fahrenheit readout
- 0.2 °C (0.5 °F) resolution for precise readings
- Backlight for use in dark areas
- Automatic sleep mode extends battery life
- Alkaline batteries provide 4000 typical measurements



Created for HVAC and facility maintenance work.

Rugged multimeter with a built-in thermometer plus a Fluke compact clamp meter to reach tight spaces. Includes test leads and a durable carrying case.

Ordering Information

Fluke 16/322 Kit

HVAC Multimeter and Clamp Meter Combo Kit

Fluke 16 Digital Multimeter with Temperature

- One rugged instrument for both temperature and electrical measurements
- Test flame rod circuits with microamp function
- Measures up to 10,000 microfarads to test motor start and run capacitors
- MIN/MAX recording with relative time stamp for up to 100 hours
- Temperature probe and test leads included
- Continuity, diode test and resistance

Fluke 322 Compact Current Clamp

- Precise low current measurements with better than 2 % basic accuracy
- 400.0 A ac range
- 600 V ac and dc ranges
- 400.0 ohm range
- 600 V CAT III electrical safety rating
- Controls positioned for one-handed operation
- Auto shut-off, display hold

Buy a
Combo Kit
and Save over
\$50* (U.S.)

FLUKE®



Created for industrial and commercial electrical work.

Rugged true-rms multimeter with a built-in thermometer plus a Fluke voltage detector. Includes ultra flexible, heat resistant test leads with interchangeable probes and clips and a temperature probe packaged in a durable carrying case.

Ordering Information

Fluke 179/1AC Kit

Electrician's Multimeter, Voltage Tester and Deluxe Accessory Combo Kit

Fluke 179 True-rms Digital Multimeter with Temperature

- True-rms voltage and current in a rugged package
- 1000 V ac and dc ranges
- Larger, easy-to-read display
- 0.09 % accuracy. 3 times better than the original Fluke 70 Series
- Backlight for use in dark areas
- Current measurements to 10 A, 20 A for 30 sec.
- Resistance and continuity
- Frequency and capacitance
- Min/Max to capture intermittent readings
- Built in thermometer – probe included
- Attach to steel surfaces with optional TPAK magnetic hanging kit
- 1000 V CAT III electrical safety rating
- Limited lifetime warranty

AC220 SureGrip™ Alligator Clips

- Insulated, nickel plated jaws grip up to .375 inches
- Blunt tip grabs round screw heads

TP220 SureGrip™ Industrial Test Probes

- Sharp, .5 inch stainless steel tip provides reliable contact
- Flexible finger barrier improves grip

TL224 SureGrip™ Silicone Test Leads

- 1.5 meter silicone-insulated wire resists heat & cold
- Reinforced strain relief

1AC VoltAlert™ Voltage Detector

- Easy-to-use voltage detector
- Fits in a shirt pocket
- All outer surfaces are non-conductive for safety
- Detects voltage without metallic contact



Created for commercial and residential electrical work.

Compact multimeter to safely measure up to 600 V plus a Fluke compact clamp meter to reach tight spaces. Includes test leads and a durable carrying case.

Ordering Information

Fluke 112/322 Kit

Electrician's Multimeter and Clamp Meter Combo Kit

Fluke 112 True-rms Digital Multimeter

- Display backlight for dark spaces
- True-rms ac voltage and current measurement
- 10 A current range (20 A for 30 sec)
- 6000-count display
- 0.7 % basic dc accuracy
- 600 V ac and dc
- 600 V CAT III electrical safety rating
- Compatible with optional Fluke Magnetic Hanging Kit
- Includes TL75 Test Leads

Fluke 322 Compact Current Clamp

- Precise low current measurements with better than 2 % basic accuracy
- 400.0 A ac range
- 600 V ac and dc ranges
- 400.0 ohm range
- 600 V CAT III electrical safety rating
- Controls positioned for one-handed operation
- Auto shut-off, display hold

Visit www.fluke.com for more information or to test drive a Fluke DMM or Clamp Meter. Call **1-800-44-FLUKE** (U.S.) or 425-446-5500 (outside the U.S.) to find a dealer near you.

Fluke. Keeping your world up and running.

©2003 Fluke Corporation. All rights reserved. Printed in U.S.A. 8/2003 2105571 F-ENG-N Rev A

*Save over \$50 off U.S. MSRP compared to buying products individually