


**Limited
 Lifetime
 Warranty!**

Keep your Fluke meter
 up and running

For 20, 70 & 80 Series
 DMMs Only

88 Deluxe Automotive Multimeter with RPM



The Fluke 88 is a complete automotive diagnostic package. It offers virtually everything you need in an automotive multimeter.

Features

- Volts, ohms, amps, continuity and diode test
- Milliseconds pulse width measurements
- RPM measurements with inductive pickup
- Min/Max/Avg recording
- Frequency and duty cycle measurements
- Lo-Ohms function
- Change Alert™
- Smoothing™
- Backlit display
- Rugged, Hard-Shell Carrying Case
- Deluxe Test Leads with interchangeable Test Probes and Wide Jaw Alligator Clips
- Sleep mode
- 10 Megohm input impedance

Specifications

Basic Accuracy (± % of reading)			
Function	Range	Accuracy	Best Resolution
DC Voltage	400 mV - 1000V	0.15%	0.1 mV
AC Voltage	400 mV - 1000V	1.5%	0.1 mV
DC Current	40 mA - 10A	0.8%	0.01 mA
AC Current	40 mA - 10A	0.8%	0.01 mA
Ohms	400Ω - 40 MΩ	0.2%	0.1 Ω, 0.01 Ω in Lo-Ohms mode
Frequency	199.99 Hz to 199.99 kHz	0.01%	0.01 Hz

Safety

Designed to protection Class II per IEC 348, ANSI/ISA-S82, CSA C22.2 No. 231, and UL 1244. Shock and vibration per MIL-T-28800 for a Class 2 instrument.

Fuse information

Uses 1A (871207 or 871210) and 15A (892583, 871223 or 847793) replaceable internal fuses.

Warranty

Lifetime (Meter)
 1 year (Accessories)

Included with Your Fluke 88 Automotive Multimeter

Fluke 88	Automotive Multimeter
C81Y	Protective Yellow Holster with Flex-Stand™ 9V Battery (Installed)
RPM80	Inductive Pickup for RPM measurements
C800	Rugged, Hard-Shell Carrying Case User's Manual Quick Reference Guide
TL24	Flexible Test Leads
TP20	Industrial Test Probes
AC85	Large Jaw Alligator Clips