


Model 18 Automotive Multimeter

Rugged, easy-to-use DMM; ideal for basic automotive applications



The rugged, easy-to-use meter for your most common measurements. 80% of automotive electrical measurements are volts, ohms, and continuity. Now you can get all these functions and more in a Fluke meter that's simple, tough, and affordable.

- 4000 count digital display
- Volts ac
- Volts dc
- Ohms
- Continuity beeper
- Sleep mode to conserve battery
- Min/Max with time stamp
- Continuity Capture™ locates intermittent opens and shorts as brief as 250 μs and identifies them in a symbolic display as a short-to-open or open-to-short transition

- Great for chasing wire and connector intermittents
- Four ranges of capacitance
- TL75 Test Leads and AC70A Alligator Clips included with meter
- High visibility yellow C10 Holster absorbs shocks and protects the meter

Battery life: Alkaline, 650 hours continuous, sleep mode

Size:
 142.3 mm L x 70.5 mm W x 34.6 mm D
 (5.55 in L x 2.75 in W x 1.35 in D)

Weight:
 10 oz (286 gm)

Two year warranty

Specifications

Function	Range and Resolution	Best Accuracy
VDC	4.000V, 40.00V, 400.0V, 600V, 4000 mV*	0.9% + 1
VAC	4.000V, 40.00V, 400.0V, 600V, 4000 mV*	1.9% + 3
Resistance	400.0Ω, 4.000 kΩ, 40.00 kΩ, 4.000 MΩ, 40.00 MΩ	0.9% + 1
Capacitance	1.00 μF, 10.00 μF, 100.0 μF, 1000 μF**	1.9% + 2
Continuity	Beeper sounds for contact <25Ω, for contacts ≥250 ms	

*The 4000 mV range can only be entered in manual range mode.
 Use the 4000 mV range with accessories.

** Overrange to 10,000 μF.

Ordering and Accessories Information

Ordering Information
 Fluke 18 Automotive Multimeter

Included Accessories
 TL75 Hard Point™ Test Leads,
 AC70A Alligator Clips, C10 Holster
 with built-in stand and hanger-
 loop, a 9 volt battery (installed)
 and owner's manual.

Need Technical Assistance? Call:
1-800-44-FLUKE
 Toll-free in the U.S.
 (905) 890-7600 in Canada
 (425) 356-5500 other countries

Fluke. *Keeping your world up and running.*