



FLUKE®

Fluke HVAC/IAQ Tools.

Get more done.

Get more done.

Fluke HVAC/IAQ Tools.

At Fluke we understand your need to quickly, accurately, and safely troubleshoot and maintain HVAC equipment.

We offer a family of quality HVAC tools that cover the systems you service and install today. And, they are always the rugged, reliable tools that professionals, such as you, can count on, again and again.

New

902 True-rms HVAC Clamp Meter

- Capture flue gas temperatures
- Conduct flame rod testing
- Measure start and run motor capacitors
- Includes true-rms



New



971 Temperature Humidity Meter

- Monitor indoor comfort conditions.
- Fast settling humidity sensor (< 60 seconds)
- Instantly calculates wet bulb and dewpoint temperatures
- Rugged and reliable



16 Digital Multimeter

- Compact DMM and thermometer in one
- Measures volts, ohms, capacitance, temperature, and microamps
- V-Check automatically switches meter to proper measurement for ohms or continuity



New


561 HVAC Pro IR Thermometer

- Check superheat, subcool, and more.
- Contact and non-contact temperature in one tool
- 12:1 spot to distance ratio lets you measure from farther away
- Adjustable emissivity assures accuracy with a variety of surface types



CO-220 Carbon Monoxide Meter

- Quickly and accurately measure dangerous CO levels
- Latest generation of electrochemical sensor detects from 0 to 999 ppm
- Responds very quickly to ambient change in carbon monoxide concentration without the use of a pump



The New Fluke 902 True-rms Clamp Meter delivers what you need to diagnose and repair HVAC systems. With true-rms technology and a CAT III 600V rating in a rugged, reliable case, the Fluke 902 is an essential part of any HVAC/R professional's toolkit.

Key Features

- Capacitance
- DC Current (µA)
- Contact Temperature
- True-rms
- Min/Max



Fluke 902 comes complete with the following:

- (2) AA alkaline batteries
- Users manual (w/ safety information)
- Soft carrying case
- (1 pair) TL75 Test Leads
- (1) 80BK Integrated DMM Temperature Probe



Optional Accessories:



H3 Clamp Meter Holster



TL223 Sure Grip Electrical Test Lead Set



Fluke. Keeping your world up and running.™

Fluke Corporation
PO Box 9090, Everett, WA USA 98206

Fluke Europe B.V.
PO Box 1186, 5602 BD Eindhoven, The Netherlands

For more information call:
In the U.S.A. (800) 443-5853 or Fax (425) 446-5116
In Europe/M-East/Africa +31 (0) 40 2675 200 or Fax +31 (0) 40 2675 222
In Canada (800)-36-FLUKE or Fax (905) 890-6866
From other countries +1 (425) 446-5500 or Fax +1 (425) 446-5116
Web access: <http://www.fluke.com>