








# Process Tools Quick Reference Guide

						
771	707	789	715	719	726	744
<b>771</b>	<b>705, 707</b>	<b>787, 789</b>	<b>712, 714, 715, 717, 718</b>	<b>719</b>	<b>725, 726</b>	<b>741, 743, 744</b>
Clamp	Loop Calibrator	Process Meter	Single Function Calibrator	Pressure Calibrator	Multi-function Calibrator	Documenting Calibrator
						<b>744</b>
		<b>787, 789</b>				<b>741, 743, 744</b>
			<b>712, 714</b>		<b>725, 726</b>	<b>741, 743, 744</b>
			<b>717, 718</b>	<b>719</b>	<b>725, 726</b>	<b>741, 743, 744</b>
<b>771</b>	<b>705, 707</b>	<b>789</b>	<b>715</b>	<b>719</b>	<b>725, 726</b>	<b>741, 743, 744</b>

## Legend

Hart	Light Blue
Document	Yellow
Electrical: volts, ohms, amps, frequency	Green
Temperature	Orange
Pressure	Red
Loop	Blue



## Application Notes

[www.fluke.com/appnotes](http://www.fluke.com/appnotes)

Fluke has a complete library of application notes and white papers on topics ranging from predictive maintenance to maintaining motors and drives to automotive troubleshooting and more.

# Fluke Pressure Calibrators

**New**



## New! 719 Electric Pressure Calibrator

Forget the hassle of hand-pumping with the innovative, built-in electric pump. Now you can calibrate and test pressure devices quickly, easily with one hand, saving you valuable time.

Use the programmable pump limit settings to eliminate over-pressurization, and to set 'pump to' pressure values. The unique cleanout port design reduces pump failures, and makes the 719 easy to clean without repairs. The compact, lightweight form, combined with one-handed use, makes this pressure calibrator the ideal tool for busy process professionals.



## Fluke 717 Series Pressure Calibrators

717 calibrators deliver outstanding performance, durability and reliability. These calibrators are compact, lightweight, and easy to carry. With a push button interface the 717s are easy to use. They are EMI tolerant, dust and splash resistant, and feature a removable battery door for quick battery changes.

These calibrators come in 9 models measuring pressure up to 5000 psi/345 bar and are compatible with Fluke 700Pxx differential, gage and absolute pressure modules to increase functionality.

For more information on these tools plus the full line of Fluke process tools go to [www.fluke.com/process](http://www.fluke.com/process).



## Fluke 718 Series Pressure Calibrator

The Fluke 718 pressure calibrator family (includes 4 models) provide a total pressure calibration solution for transmitters, gauges and switches.

This compact pressure calibration solution is about a third of the size of comparable instruments and weighs just one kilogram (two pounds). The unique easy to clean pump helps protect the pump from damage and provides the ability to service the pump without disassembly, even in the field.

**Fluke.** *Keeping your world up and running.*®

**Fluke Corporation**  
PO Box 9090, Everett, WA USA 98206

**Fluke Europe B.V.**  
PO Box 1186, 5602 BD  
Eindhoven, The Netherlands

**For more information call:**  
In the U.S.A. (800) 443-5853 or  
Fax (425) 446-5116  
In Europe/M-East/Africa (31 40) 2 675 200 or  
Fax (31 40) 2 675 222  
In Canada (800)-36-FLUKE or  
Fax (905) 890-6866  
From other countries +1 (425) 446-5500 or  
Fax +1 (425) 446-5116  
Web access: <http://www.fluke.com>

©2008 Fluke Corporation.  
Specifications subject to change without notice.  
Printed in U.S.A. 8/2008 3362253 F-EN-N Rev C

**Modification of this document is not permitted without written permission from Fluke Corporation.**