

Fluke 434/PWR Power Analyzer

The easy way to perform energy consumption studies

Technical Data

Load studies and energy assessments

- Monitor maximum power demand over user-defined averaging periods
- Demonstrate the benefit of efficiency improvements with energy consumption tests
- Measure harmonic distortion caused by electronic loads
- Analyze reliability problems by capturing voltage dips and swells from load switching


The Fluke 434/PWR power analyzer is the ideal tool for finding energy waste in commercial and factory buildings and equipment. Electricians, field service engineers and maintenance technicians can use this special edition instrument to conduct energy consumption studies and electrical load analysis, and to perform power quality logging and analysis according to EN 50160. Fluke's 434/PWR is a complete three-phase troubleshooting tool that measures virtually every power system parameter: voltage, current, frequency, power, energy consumption, $\cos \phi$ or power factor, unbalance, and harmonics and inter-harmonics.

- Captures events like dips and swells, interruptions and rapid voltage changes, based upon 1/2 cycle rms values
- Unique AutoTrend gives you fast insight into changes over time
- With a single push of a button, the unique System Monitor gives you an overview of power system performance. It also checks that incoming power complies to EN50160 limits or to your own custom specifications
- Logger: detailed, user-configurable long-term recording gives you the MIN, MAX and AVG readings of up to 100 parameters on all four phases. Averaging time can be selected down to 0.5 seconds (or 1 minute for 1 day's recording, 10 minutes for 1 week, 30 minutes for 1 month or more)
- Two groups of four channels: simultaneously measure voltage and current on all three phases and neutral




- Auto Scaling: easier trend analysis with automatic scaling of the vertical axis—so you will always view the waveforms on a full display
- Meets the stringent 600 V CAT IV, 1000 V CAT III safety standard required for measurements at service entrance
- Extensive data analysis: cursors and zoom can be used 'live' while taking the measurements, or 'offline' on stored measurement data. The stored measurements can also be transferred to Power Log software


Analyze all parameters on display




Measure and record power (W), VA and VARs. The Fluke 434/PWR adds the ability to record energy consumption.




Logging function allows you to customize measurement selections and provides analysis of user-selectable parameters to find intermittent problems or relate PQ issues to other phenomena/events.




The System-Monitor overview screen gives instant insight into whether the voltage, harmonics, frequency, and the number of dips and swells fall outside the set limits.



Phasor diagram shows voltage and current unbalance, and helps verify connections.




The full color display allows the use of industry-standard color-coding (user selectable) to correlate measurements with actual wiring.



Fluke Power Log Software

Designed to quickly view recorded data, the built-in Power Log software displays all recorded parameters on interactive trends. Generate a professional looking report with the 'PRINT' function or copy and paste images into a report document manually. Customize the report generator to easily create your own formats.



Print reports and view graphics with Power Log software.

Technical specifications

Inputs		
Number of inputs	4 voltage and current (3 phases + neutral)	
Maximum input voltage	1000 Vrms (6 kV peak)	
Maximum sampling speed	200 kS/s on each channel simultaneously	
Volts/Amps/Hertz	Measurement range	Accuracy
Vrms (AC+DC)	1 V to 1000 V	0.5 % of Vnom
Vpeak	1 V to 1400 V	5 % of Vnom
Voltage Crest Factor (CF)	1.0 to > 2.8	± 5 %
Arms (AC + DC)	0 to 20 kA	± 0.5 % ± 5 counts
Apeak	1.4x rms value	5 %
Crest factor, A	1 to 10	± 5 %
Hz 50 Hz nominal	40 Hz to 70 Hz	± 0.01 Hz
Dips and swells		
Vrms (AC+DC) ²	0.0 % to 100 % of Vnom	± 0.2 % of nominal voltage
Arms (AC+DC) ²	0 to 20 kA	± 1 % ± 5 counts
Harmonics		
Harmonic (interharmonic)	DC, 1 to 50; (Off, 1..49) measured according to IEC 61000-4-7	
Vrms	0.0 to 1000 V	± 0.05 % of nominal voltage
Arms	0.0 to 4000 mV x clamp scaling	± 5 % ± 5 counts
Watts	Depends on clamp scaling and voltage	± 5 % ± n x 2 % or reading, ± 10 counts
DC voltage	0.0 to 1000 V	± 0.2 % of nominal voltage
THD	0.0 to 100.0 %	± 2.5 % V and A (± 5 % Watt)
HZ	0 to 3500 Hz	± 1 Hz
Phase angle	-360° to +360°	± n × 1.5°
Power and energy		
Watt, VA, VAR	1.0 to 20.00 MVA ¹	± 1 % ± counts
kWh, kVAh, kVARh	00.00 to 200.0 GVAh ¹	± 1.5 % ± 10 counts
Power factor/Cos Φ/DPF	0 to 1	± 0.03
Unbalance		
Volts	0.0 to 5.0 %	± 0.5 %
Current	0.0 to 20 %	± 1 %
Autotrend recording		
Sampling	5 readings/sec continuous sampling per channel	
Memory	1800 min, max and avg points for each reading	
Recording time	Up to 450 days	
Zoom	Up to 12x horizontal zoom	
Logging		
Sampling	5 readings/sec continuous sampling per channel	
Readings	User selectable up to 100 readings on 3 phases and neutral simultaneously	
Averaging	Two hours down to 0.5 s user selectable	
Recording time	User selectable up to 7 MB of shared memory	
Zoom	Yes	
Memory		
Screens and data	50, shared memory divided between logging, screens and data sets	
General specifications		
Operating temperature	0 °C to +50 °C	
Safety	EN61010-1 (2nd edition) pollution degree 2; 1000 V CAT III/600 V CAT IV ANSI/ISA S82.01	
Size	256 mm x 169 mm x 64 mm	
Weight	2 kg	
Battery life	Rechargeable NiMH pack (installed): > 7 hours Battery charging time: 4 hours typical	
Shock	30 g	
Vibration	3 g according to MIL-PRF-28800F Class 2	
Case	Rugged, shock proof with integrated protective holster, IP51 (drip and dust proof)	
Warranty	Three-year	

1) Depending on clamp scaling

2) Value is measured over 1 cycle, commencing at a fundamental zero crossing, and refreshed each half-cycle

Ordering information

Fluke 434/PWR Power Analyzer
(special edition for energy analysis)

Includes:

Fluke 434/PWR Power Analyzer
i430-Flexipack 4 current clamps
5 Test leads, 4 black, 1 green
5 Alligator clips, 4 black, 1 green
BC430 Battery charger eliminator
Power Log Software OC4USB
Optical cable for USB
WC100 Color localization set
Getting Started Manual
Users Manual on CD-ROM



Fluke. *Keeping your world
up and running.*®

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

Fluke Europe B.V.
PO Box 1186, 5602 BD
Eindhoven, The Netherlands

For more information call:
In the U.S.A. (800) 443-5853 or
Fax (425) 446-5116
In Europe/M-East/Africa +31 (0) 40 2675 200 or
Fax +31 (0) 40 2675 222
In Canada (800)-36-FLUKE or
Fax (905) 890-6866
From other countries +1 (425) 446-5500 or
Fax +1 (425) 446-5116
Web access: <http://www.fluke.com>

©2011 Fluke Corporation.
Specifications subject to change without notice.
Printed in U.S.A. 7/2011 4093772A D-EN-N

**Modification of this document is not permitted
without written permission from Fluke Corporation.**