

Instrument Security Procedures

Models:

750P00, 750P01, 750P02, 750P22, 750P03, 750P23, 750P04, 750P24,
750P05, 750P06, 750P27, 750P07, 750P08, 750P09, 750P2000, 750P29,
750P30, 750P31, 750PA3, 750PA4, 750PA5, 750PA6, 750PA27, 750PA7,
750PA8, 750PA9, 750PV3, 750PV4, 750PD2, 750PD3, 750PD10,
750PD4, 750PD5, 750PD50, 750PD6, 750PD7, 750PD27, 750R04,
750R06, 750R27, 750R07, 750R08, 750R29, 750R30, 750R31, 750RD5,
750RD6, 750RD27, 750P3IN, 750P5IN, 750P01Ex, 750P24Ex, 750P05Ex,
750P06Ex, 750P27Ex, 750P09Ex, 750P29Ex, 750PA4Ex

Product Name:

Fluke 750P/750R, 750PEX Pressure Module

Instrument Description:

Pressure module series measuring pressure from 1 inch H2O to 10,000 psi.

Memory Description:

Microprocessor flash:

64 Kbytes

Microprocessor RAM:

6 Kbytes

Memory Cleaning Instructions:

There is no user accessible memory. A programming device is necessary to access memory.