

Choose your free gift with purchase of a Fluke 754 or Fluke 753 Documenting Process Calibrator

Fluke 700G Precision Pressure Test Gauges		
Model #	Item #	Description
FLUKE-700G04	4096972	PRESSURE GAUGE, 15 PSIG / 103 kPa
FLUKE-700G05	4097514	PRESSURE GAUGE, 30 PSIG / 207 kPa
FLUKE-700G06	4097538	PRESSURE GAUGE, 100 PSIG / 690 kPa
FLUKE-700G07	4097561	PRESSURE GAUGE, 500 PSIG / 3400 kPa
FLUKE-700G08	4097592	PRESSURE GAUGE, 1,000 PSIG / 6900 kPa
FLUKE-700G27	4097545	PRESSURE GAUGE, 300 PSIG / 2070 kPa
FLUKE-700G29	4097605	PRESSURE GAUGE, 3,000 PSIG / 20.7 M Pa
FLUKE-700G30	4097610	PRESSURE GAUGE, 5,000 PSIG / 34 M Pa
FLUKE-700G31	4097622	PRESSURE GAUGE, 10,000 PSIG / 69 M Pa

Fluke 700P Pressure Modules		
Model #	Item #	Description
Differential		
FLUKE-700P00	667391	PRESSURE MODULE, 1 IN.H2O DIFF / 0.25 kPa
FLUKE-700P01	936005	PRESSURE MODULE, 10 IN. H2O DIFF / 2.5 kPa
FLUKE-700P02	936013	PRESSURE MODULE, 1 PSID / 6900 Pa
FLUKE-700P03	936018	PRESSURE MODULE, 5 PSID / 34 kPa
FLUKE-700P04	936021	PRESSURE MODULE, 15 PSID / 103 kPa
FLUKE-700P22	100138	PRESSURE MODULE, 1 PSID, WET / 6900 Pa
FLUKE-700P23	100146	PRESSURE MODULE, 5 PSID, WET / 34 kPa
FLUKE-700P24	100153	PRESSURE MODULE, 15 PSID, WET / 103 kPa
Gauge		
FLUKE-700P05	936026	PRESSURE MODULE, 30 PSIG / 207 kPa
FLUKE-700P06	936034	PRESSURE MODULE, 100 PSIG / 690 kPa
FLUKE-700P07	936039	PRESSURE MODULE, 500 PSIG / 3400 kPa
FLUKE-700P08	936042	PRESSURE MODULE, 1000 PSIG / 6900 kPa
FLUKE-700P09	617123	PRESSURE MODULE 1500PSIG / 10 MPa
FLUKE-700P27	1549399	PRESSURE MODULE, 300 PSIG / 2070 kPa
Absolute		
FLUKE-700PA3	612207	PRESSURE MODULE 5PSIA / 34 kPa
FLUKE-700PA4	612215	PRESSURE MODULE 15PSIA / 103 kPa
FLUKE-700PA5	612223	PRESSURE MODULE 30PSIA / 207 kPa
FLUKE-700PA6	612231	PRESSURE MODULE 100PSIA / 690 kPa
Vacuum		
FLUKE-700PV3	612249	PRESSURE MODULE -5PSI / -34 kPa
FLUKE-700PV4	612256	PRESSURE MODULE -15PSI / -103 kPa
Dual		
FLUKE-700PD2	612090	PRESSURE MODULE +/-1 PSID / ±6900 Pa
FLUKE-700PD3	612108	PRESSURE MODULE +/-5 PSID / ±34 kPa
FLUKE-700PD4	606837	PRESSURE MODULE, +/-15PSID / ±103 kPa
FLUKE-700PD5	612116	PRESSURE MODULE -15+30 PSIG / -100/207 kPa
FLUKE-700PD6	612124	PRESSURE MODULE -15+100PSIG / -100/690 kPa
FLUKE-700PD7	612132	PRESSURE MODULE -15+200PSIG / -100/1380 kPa
High		
FLUKE-700P29	612157	PRESSURE MODULE, 3000PSIG WET / 20.7 M Pa
FLUKE-700P30	612165	PRESSURE MODULE, 5000PSIG WET / 34 M Pa
FLUKE-700P31	612173	PRESSURE MODULE, 10000PSIG WET / 69 M Pa