



Electrical applications



Fluke 114

Best for
Basic electrical troubleshooting.

Electrical troubleshooting
Designed for easy, one-hand operation, the perfect tool for “go/no” go testing.

[More product information »](#)



Fluke 117

Best for
Wide variety of electrical work.

Electrical maintenance troubleshooting
When you need to eliminate false or “ghost” voltages or perform continuity, connection or basic wiring checks.

Non-contact voltage detection
Integrated non-contact voltage detection simplifies many tasks.

[More product information »](#)



Fluke 233

Best for
Applications where display positioning is problematic.

Remote monitoring
View meter display up to 30 feet away from the measurement point. Observe meter real-time readings remotely.

Unusual measurements
Remote magnetic display solves separation problems.

Electrical maintenance
All the features and functions of a conventional multimeter.

[More product information »](#)



Fluke CNX 3000

Best for
Applications where live measurements from multiple modules simultaneously and remotely are necessary.

Applications

- Production test
- Reduce Arc Flash potential
- Preventative maintenance checks
- Lighting systems
- Maintaining UPS systems or backup power
- Data centers

Remote monitoring

The CNX wireless enabled modules measure ac voltage, ac current and temperature, which display on the CNX 3000 Wireless Multimeter.

[More product information »](#)