



## HVAC applications



### Fluke 116

**Best for**  
HVAC troubleshooting.

#### Residential HVAC maintenance

Lower voltage HVAC residential maintenance, installation and troubleshooting.

#### Temperature and microamp measurements

Troubleshooting problems with HVAC equipment and flame sensors.

[More product information »](#)



### Fluke 233

**Best for**  
Applications where display positioning is problematic.

#### Remote monitoring

View meter display up to 30 feet away from the measurement point. Observe meter real-time readings remotely.

#### Unusual measurements

Remote magnetic display solves separation problems.

#### Electrical maintenance

All the features and functions of a conventional multimeter.

[More product information »](#)



### Fluke CNX 3000 HVAC system

**Best for**  
Applications where live measurements from multiple modules simultaneously and remotely are necessary.

#### Applications

- Rooftop units
- Chillers
- Boilers
- Heat pumps
- Make up air systems
- Vent temperatures
- Air compressors

#### Remote monitoring

The CNX wireless enabled modules measure ac voltage, ac current and temperature, which display on the CNX 3000 Wireless Multimeter.

[More product information »](#)