



Utilities applications

FLUKE®



Fluke 113

Best for

Revenue meter tests involving meter sets and re-connections, capacitor checks, detection of absence or presence of voltage, and for continuity, connections or basic wiring checks.

Simultaneous voltage and continuity checks

VCHEK™ LoZ low impedance function allows users to check voltage and continuity simultaneously.

[More product information »](#)

Fluke 233

Best for

Applications where display positioning is problematic.

Remote monitoring

View meter display up to 30 feet away from the measurement point. Observe meter real-time readings remotely.

Unusual measurements

Remote magnetic display solves separation problems.

Electrical maintenance

All the features and functions of a conventional multimeter.

[More product information »](#)

Fluke CNX 3000

Best for

Applications where live measurements from multiple modules simultaneously and remotely are necessary.

Applications

- Three-phase load checks and load balance
- Reduce Arc Flash potential

Remote monitoring

The CNX wireless enabled modules measure ac voltage, ac current and temperature, which display on the CNX 3000 Wireless Multimeter.

[More product information »](#)