



## Automotive applications



### Fluke 88V

**Best for**  
Automotive troubleshooting.

**Troubleshoot variety of problems on conventional and hybrid vehicles**

Millisecond pulse width measurements for fuel injectors, RPM readings for both DIS and conventional ignitions with optional inductive pickup.

**Automotive testing**

Alternator diodes, duty cycle, solenoids, breaker points, wiring, switches, and more.

[More product information »](#)



### Fluke 233

**Best for**  
Applications where display positioning is problematic.

**Remote monitoring**

View meter display up to 30 feet away from the measurement point. Observe meter real-time readings remotely.

**Unusual measurements**

Remote magnetic display solves separation problems.

**Electrical maintenance**

All the features and functions of a conventional multimeter.

[More product information »](#)



### Fluke CNX 3000

**Best for**  
Applications where live measurements from multiple modules simultaneously and remotely are necessary.

**Applications**

- Overcome separation issues between measurement points and/or controls
- Easily see cause and effect

**Remote monitoring**

The CNX wireless enabled modules measure ac voltage, ac current and temperature, which display on the CNX 3000 Wireless Multimeter.

[More product information »](#)