



## Electrical applications



### Fluke 114

**Best for**  
Basic electrical troubleshooting.

**Electrical troubleshooting**  
Designed for easy, one-hand operation, the perfect tool for “go/no” go testing.

[More product information »](#)



### Fluke 117

**Best for**  
Wide variety of electrical work.

**Electrical maintenance troubleshooting**  
When you need to eliminate false or “ghost” voltages or perform continuity, connection or basic wiring checks.

**Non-contact voltage detection**  
Integrated non-contact voltage detection simplifies many tasks.

[More product information »](#)



### Fluke 233

**Best for**  
Applications where display positioning is problematic.

**Remote monitoring**  
View meter display up to 30 feet away from the measurement point. Observe meter real-time readings remotely.

**Unusual measurements**  
Remote magnetic display solves separation problems.

**Electrical maintenance**  
All the features and functions of a conventional multimeter.

[More product information »](#)



### Fluke CNX 3000

**Best for**  
Applications where live measurements from multiple modules simultaneously and remotely are necessary.

**Applications**

- Production test
- Reduce Arc Flash potential
- Preventative maintenance checks
- Lighting systems
- Maintaining UPS systems or backup power
- Data centers

**Remote monitoring**

The CNX wireless enabled modules measure ac voltage, ac current and temperature, which display on the CNX 3000 Wireless Multimeter.

[More product information »](#)