



# Utilities applications

**FLUKE®**



## Fluke 113

### Best for

Revenue meter tests involving meter sets and re-connections, capacitor checks, detection of absence or presence of voltage, and for continuity, connections or basic wiring checks.

### Simultaneous voltage and continuity checks

VCHEK™ LoZ low impedance function allows users to check voltage and continuity simultaneously.

[More product information »](#)

## Fluke 233

### Best for

Applications where display positioning is problematic.

### Remote monitoring

View meter display up to 30 feet away from the measurement point. Observe meter real-time readings remotely.

### Unusual measurements

Remote magnetic display solves separation problems.

### Electrical maintenance

All the features and functions of a conventional multimeter.

[More product information »](#)

## Fluke CNX 3000

### Best for

Applications where live measurements from multiple modules simultaneously and remotely are necessary.

### Applications

- Three-phase load checks and load balance
- Reduce Arc Flash potential

### Remote monitoring

The CNX wireless enabled modules measure ac voltage, ac current and temperature, which display on the CNX 3000 Wireless Multimeter.

[More product information »](#)