



## Utilities applications



### Fluke 113

**Best for**  
Revenue meter tests involving meter sets and re-connections, capacitor checks, detection of absence or presence of voltage, and for continuity, connections or basic wiring checks.

#### Simultaneous voltage and continuity checks

VCHEK™ LoZ low impedance function allows users to check voltage and continuity simultaneously.

[More product information »](#)



### Fluke 233

**Best for**  
Applications where display positioning is problematic.

#### Remote monitoring

View meter display up to 30 feet away from the measurement point. Observe meter real-time readings remotely.

#### Unusual measurements

Remote magnetic display solves separation problems.

#### Electrical maintenance

All the features and functions of a conventional multimeter.

[More product information »](#)



### Fluke CNX 3000

**Best for**  
Applications where live measurements from multiple modules simultaneously and remotely are necessary.

#### Applications

- Three-phase load checks and load balance
- Reduce Arc Flash potential

#### Remote monitoring

The CNX wireless enabled modules measure ac voltage, ac current and temperature, which display on the CNX 3000 Wireless Multimeter.

[More product information »](#)