



HVAC applications



Fluke 116

Best for
HVAC troubleshooting.

Residential HVAC maintenance

Lower voltage HVAC residential maintenance, installation and troubleshooting.

Temperature and microamp measurements

Troubleshooting problems with HVAC equipment and flame sensors.

[More product information »](#)



Fluke 233

Best for
Applications where display positioning is problematic.

Remote monitoring

View meter display up to 30 feet away from the measurement point. Observe meter real-time readings remotely.

Unusual measurements

Remote magnetic display solves separation problems.

Electrical maintenance

All the features and functions of a conventional multimeter.

[More product information »](#)



Fluke CNX 3000 HVAC system

Best for
Applications where live measurements from multiple modules simultaneously and remotely are necessary.

Applications

- Rooftop units
- Chillers
- Boilers
- Heat pumps
- Make up air systems
- Vent temperatures
- Air compressors

Remote monitoring

The CNX wireless enabled modules measure ac voltage, ac current and temperature, which display on the CNX 3000 Wireless Multimeter.

[More product information »](#)