

Fluke Calibration Products Eligible for Accurate Power of Fluke Promotion

MODEL	Fluke Part Number	DESCRIPTION
525A/CASE	1777605	TRANSIT CASE
525B/A0 120V	4307718	TEMPERATURE/PRESSURE CALIBRATOR, NAMERICA
HART-5699F	2068693	SPRT 220-660C 19 INCH W/LEMO CONNECTOR, CAL CERT
Y525	1622027	RACK MOUNT KIT
P3010SK	3891201	SEAL KIT, P3010 SERIES
P3020SK	3891212	SEAL KIT, P3020 SERIES
P3030SK	3891220	SEAL KIT, P3030 SERIES
P3100SK	3891108	SEAL KIT, P3100 SERIES
P5514SK	3891113	SEAL KIT,P5514
P5514SK-EP	3891136	ETHYLENE PROPYLENE SEAL KIT, P5514-EP
P5514SK-V	3891124	VITON SEAL KIT, P5514-V
P5515SK	3891149	SEAL KIT, P5515
P5515SK-EP	3891172	ETHYLENE PROPYLENE SEAL KIT, P5515-EP
P5515SK-V	3891160	VITON SEAL KIT, P5515-V
P5521SK	3891185	SEAL KIT,P5521
P5522SK	3891197	SEAL KIT,P5522
P5523SK	4105701	SEAL KIT, P5523 LIQUID TO GAS INTERFACE
884X-4GB	4121552	USB MEMORY, 4GB
2700G-BG100K	4152258	REFERENCE PRESSURE GAUGE BG100K
2700G-BG100K/C	4334015	REFERENCE PRESSURE GAUGE BG100K W/ ACCREDITATION
2700G-BG200K	4152264	REFERENCE PRESSURE GAUGE BG200K
2700G-BG200K/C	4334026	REFERENCE PRESSURE GAUGE BG200K W/ ACCREDITATION
2700G-BG2M	4152286	REFERENCE PRESSURE GAUGE BG2M
2700G-BG2M/C	4334044	REFERENCE PRESSURE GAUGE BG2M W/ ACCREDITATION
2700G-BG3.5M	4152299	REFERENCE PRESSURE GAUGE BG3.5M
2700G-BG3.5M/C	4334059	REFERENCE PRESSURE GAUGE BG3.5M W/ ACCREDITATION
2700G-BG700K	4152273	REFERENCE PRESSURE GAUGE BG700K
2700G-BG700K/C	4334032	REFERENCE PRESSURE GAUGE BG700K W/ ACCREDITATION
2700G-BG7M	4152300	REFERENCE PRESSURE GAUGE BG7M
2700G-BG7M/C	4334067	REFERENCE PRESSURE GAUGE BG7M W/ ACCREDITATION
2700G-G20M	4152317	REFERENCE PRESSURE GAUGE G20M
2700G-G20M/C	4334071	REFERENCE PRESSURE GAUGE G20M W/ ACCREDITATION
2700G-G35M	4152321	REFERENCE PRESSURE GAUGE G35M
2700G-G35M/C	4334080	REFERENCE PRESSURE GAUGE G35M W/ ACCREDITATION
2700G-G70M	4152339	REFERENCE PRESSURE GAUGE G70M
2700G-G70M/C	4334098	REFERENCE PRESSURE GAUGE G70M W/ ACCREDITATION
3100SK-V	3875241	SEAL KIT - 31XX & 32XX,MODELS - VITON SEALS
3130-G2M	4317885	PORTABLE GAS PRESSURE CALIBRATOR, LC US,EU,UK,CHIN/AUS
3130-G2M/C	4334102	PORTABLE GAS PRESSURE CALIBRATOR, LC US,EU,UK,CHIN/AUS W/ACC CAL
55-655	3905893	ST-55 OPERATING FLUID (OIL) 1 QUART BOTTLE
6241-1.4M	4183737	PPC4E GAS PRESSURE CONTROLLER, 1.4 MPA (200 PSI)
6241-100K	4183728	PPC4E GAS PRESSURE CONTROLLER, +/-100 KPA (+/-15 PSI)
6241-14M	4183755	PPC4E GAS PRESSURE CONTROLLER, 14 MPA (2000 PSI)
6241-15K	4183719	PPC4E GAS PRESSURE CONTROLLER, +/-15 KPA (+/-2.2 PSI)
6241-7M	4183743	PPC4E GAS PRESSURE CONTROLLER, 7 MPA (1000 PSI)
6242-1.4M	4183770	PPC4EX GAS PRESSURE CONTROLLER, 1.4 MPA (200 PSI), EXTENDED RANGE
6242-100K	4183762	PPC4EX GAS PRESSURE CONTROLLER, +/-100 KPA (+/-15 PSI), EXTENDED RANGE
6242-14M	4183796	PPC4EX GAS PRESSURE CONTROLLER, 14 MPA (2000 PSI), EXTENDED RANGE
6242-7M	4183781	PPC4EX GAS PRESSURE CONTROLLER, 7 MPA (1000 PSI), EXTENDED RANGE
6531-140M	4183661	E-DWT ELECTRONIC DEADWEIGHT TESTER, 140 MPA (20K PSI)
6531-14M	4183623	E-DWT ELECTRONIC DEADWEIGHT TESTER, 14 MPA (2K PSI)
6531-200M-B	4625452	ELECTRONIC DEADWEIGHT TESTER, 40 TO 200 MPA (6K TO 30K PSI)
6531-20M	4183638	E-DWT ELECTRONIC DEADWEIGHT TESTER, 20 MPA (3K PSI)
6531-40M	4183645	E-DWT ELECTRONIC DEADWEIGHT TESTER, 40 MPA (6K PSI)
6531-70M	4183650	E-DWT ELECTRONIC DEADWEIGHT TESTER, 70 MPA (10K PSI)
6531-7M	4183614	E-DWT ELECTRONIC DEADWEIGHT TESTER, 7 MPA (1K PSI)
6532-140M	4183692	E-DWT ELECTRONIC DEADWEIGHT TESTER, 140 MPA (20K PSI), EXTENDED RANGE
6532-200M-B	4625465	ELECTRONIC DEADWEIGHT TESTER, 4 TO 200 MPA (600 TO 30K PSI)
6532-70M	4183689	E-DWT ELECTRONIC DEADWEIGHT TESTER, 70 MPA (10K PSI), EXTENDED RANGE
CWS3011-INHG	4201938	CONVERSION WEIGHT SET, VACUUM INHG
CWS3011-KPA	4201950	CONVERSION WEIGHT SET, VACUUM KPA

Offer valid through December 31, 2016. Redemptions must be sent within 30 days of purchase.

Fluke Calibration Products Eligible for Accurate Power of Fluke Promotion

CWS3011-MBAR	4201945	CONVERSION WEIGHT SET, VACUUM MBAR
CWS3011-MMHG	4201923	CONVERSION WEIGHT SET, VACUUM MMHG
CWS3012-INH2O	4201989	CONVERSION WEIGHT SET, P3012/P3013 INH2O
CWS3012-KPA	4201961	CONVERSION WEIGHT SET, P3012/P3013 KPA
CWS3012-MBAR	4201977	CONVERSION WEIGHT SET, P3012/P3013 MBAR
CWS3014-BAR	4201992	CONVERSION WEIGHT SET, P3014 BAR
CWS3014-KGCM2	4202001	CONVERSION WEIGHT SET, P3014 KG/CM2
CWS3014-KPA	4202020	CONVERSION WEIGHT SET, P3014 KPA
CWS3014-MPA	4202035	CONVERSION WEIGHT SET, P3014 MPA
CWS3014-PSI	4202012	CONVERSION WEIGHT SET, P3014 PSI
CWS3015-BAR	4202047	CONVERSION WEIGHT SET, P3015 BAR
CWS3015-KGCM2	4202058	CONVERSION WEIGHT SET, P3015 KG/CM2
CWS3015-KPA	4202073	CONVERSION WEIGHT SET, P3015 KPA
CWS3015-MPA	4202086	CONVERSION WEIGHT SET, P3015 MPA
CWS3015-PSI	4202064	CONVERSION WEIGHT SET, P3015 PSI
CWS3031-BAR	4202099	CONVERSION WEIGHT SET, P3031 BAR
CWS3031-KGCM2	4202105	CONVERSION WEIGHT SET, P3031 KG/CM2
CWS3031-KPA	4202122	CONVERSION WEIGHT SET, P3031 KPA
CWS3031-MPA	4202131	CONVERSION WEIGHT SET, P3031 MPA
CWS3031-PSI	4202110	CONVERSION WEIGHT SET, P3031 PSI
CWS3032-BAR	4202146	CONVERSION WEIGHT SET, P3032 BAR
CWS3032-KGCM2	4202154	CONVERSION WEIGHT SET, P3032 KG/CM2
CWS3032-KPA	4202179	CONVERSION WEIGHT SET, P3032 KPA
CWS3032-MPA	4202187	CONVERSION WEIGHT SET, P3032 MPA
CWS3032-PSI	4202168	CONVERSION WEIGHT SET, P3032 PSI
CWS3111-BAR	4202193	CONVERSION WEIGHT SET, P3111/P3211 BAR
CWS3111-KGCM2	4202204	CONVERSION WEIGHT SET, P3111/P3211 KG/CM2
CWS3111-KPA	4202228	CONVERSION WEIGHT SET, P3111/P3211 KPA
CWS3111-MPA	4202237	CONVERSION WEIGHT SET, P3111/P3211 MPA
CWS3111-PSI	4202219	CONVERSION WEIGHT SET, P3111/P3211 PSI
CWS3112-BAR	4202243	CONVERSION WEIGHT SET, P3112 BAR
CWS3112-KGCM2	4202255	CONVERSION WEIGHT SET, P3112 KGCM2
CWS3112-MPA	4202270	CONVERSION WEIGHT SET, P3112 MPA
CWS3112-PSI	4202262	CONVERSION WEIGHT SET, P3112 PSI
CWS3113-BAR	4202281	CONVERSION WEIGHT SET, P3113/P3114/P3213/P3214 BAR
CWS3113-KGCM2	4202296	CONVERSION WEIGHT SET, P3113/P3114/P3213/P3214 KGCM2
CWS3113-MPA	4202313	CONVERSION WEIGHT SET, P3113/P3114/P3213/P3214 MPA
CWS3113-PSI	4202308	CONVERSION WEIGHT SET, P3113/P3114/P3213/P3214 PSI
CWS3115-BAR	4202324	CONVERSION WEIGHT SET, P3115 BAR
CWS3115-KGCM2	4202336	CONVERSION WEIGHT SET, P3115 KGCM2
CWS3115-MPA	4202351	CONVERSION WEIGHT SET, P3115 MPA
CWS3115-PSI	4202349	CONVERSION WEIGHT SET, P3115 PSI
CWS3116-BAR	4202360	CONVERSION WEIGHT SET, P3116 BAR
CWS3116-KGCM2	4202372	CONVERSION WEIGHT SET, P3116 KGCM2
CWS3116-MPA	4202397	CONVERSION WEIGHT SET, P3116 MPA
CWS3116-PSI	4202385	CONVERSION WEIGHT SET, P3116 PSI
CWS3123-BAR	4202403	CONVERSION WEIGHT SET, P3123/P3124/P3223/P3224 BAR
CWS3123-KGCM2	4202415	CONVERSION WEIGHT SET, P3123/P3124/P3223/P3224 KG/CM2
CWS3123-MPA	4202432	CONVERSION WEIGHT SET, P3123/P3124/P3223/P3224 MPA
CWS3123-PSI	4202426	CONVERSION WEIGHT SET, P3123/P3124/P3223/P3224 PSI
CWS3125-BAR	4202444	CONVERSION WEIGHT SET, P3125 BAR
CWS3125-KGCM2	4202459	CONVERSION WEIGHT SET, P3125 KG/CM2
CWS3125-MPA	4202471	CONVERSION WEIGHT SET, P3125 MPA
CWS3125-PSI	4202467	CONVERSION WEIGHT SET, P3125 PSI
CWS3830-BAR	4202480	CONVERSION WEIGHT SET, P3830 BAR
CWS3830-MPA	4202500	CONVERSION WEIGHT SET, P3830 MPA
CWS3830-PSI	4202498	CONVERSION WEIGHT SET, P3830 PSI
CWS3840-BAR	4202517	CONVERSION WEIGHT SET, P3840 BAR
CWS3840-MPA	4202539	CONVERSION WEIGHT SET, P3840 MPA
CWS3840-PSI	4202521	CONVERSION WEIGHT SET, P3840 PSI
CWS3860-BAR	4202542	CONVERSION WEIGHT SET, P3860 BAR
CWS3860-MPA	4202563	CONVERSION WEIGHT SET, P3860 MPA
CWS3860-PSI	4202556	CONVERSION WEIGHT SET, P3860 PSI

Offer valid through December 31, 2016. Redemptions must be sent within 30 days of purchase.

Fluke Calibration Products Eligible for Accurate Power of Fluke Promotion

P3000H-DEMO-1	3963105	HYDRAULIC DWT DEMO KIT
P3011-INHG	4184297	VACUUM DEADWEIGHT TESTER, (-30 INHG), NO PUMP
P3011-INHG-P	4184304	VACUUM DEADWEIGHT TESTER, (-30 INHG), W/ PUMP
P3011-KPA	4184249	VACUUM DEADWEIGHT TESTER, (-100 KPA), NO PUMP
P3011-KPA-P	4184251	VACUUM DEADWEIGHT TESTER, (-100 KPA), W/ PUMP
P3011-MBAR	4184260	VACUUM DEADWEIGHT TESTER, (-1000 MBAR), NO PUMP
P3011-MBAR-P	4184285	VACUUM DEADWEIGHT TESTER, (-1000 MBAR), W/ PUMP
P3011-MMHG	4184319	VACUUM DEADWEIGHT TESTER, (-760 MMHG), NO PUMP
P3011-MMHG-P	4184328	VACUUM DEADWEIGHT TESTER, (-760 MMHG), W/ PUMP
P3012-INH2O-P	4184355	GAS DEADWEIGHT TESTER, 400 INH2O, W/ PUMP
P3012-KPA-P	4184337	GAS DEADWEIGHT TESTER, 100 KPA, W/ PUMP
P3012-MBAR-P	4184343	GAS DEADWEIGHT TESTER, 1000 MBAR, W/ PUMP
P3013-INH2O-P	4184381	GAS DEADWEIGHT TESTER, 800 INH2O, W/ PUMP
P3013-KPA-P	4184362	GAS DEADWEIGHT TESTER, 200 KPA, W/ PUMP
P3013-MBAR-P	4184370	GAS DEADWEIGHT TESTER, 2000 MBAR, W/ PUMP
P3014-BAR-P	4184396	GAS DEADWEIGHT TESTER, 10 BAR, W/ PUMP
P3014-KGCM2-P	4184409	GAS DEADWEIGHT TESTER, 10 KGF/CM2, W/ PUMP
P3014-KPA-P	4184427	GAS DEADWEIGHT TESTER, 1000 KPA, W/ PUMP
P3014-MPA-P	4184430	GAS DEADWEIGHT TESTER, 1 MPA, W/ PUMP
P3014-PSI-P	4184411	GAS DEADWEIGHT TESTER, 150 PSI, W/ PUMP
P3015-BAR	4184448	GAS DEADWEIGHT TESTER, 35 BAR, NO PUMP
P3015-BAR-P	4184453	GAS DEADWEIGHT TESTER, 35 BAR, W/ PUMP
P3015-KGCM2	4184466	GAS DEADWEIGHT TESTER, 35 KGF/CM2, NO PUMP
P3015-KGCM2-P	4184475	GAS DEADWEIGHT TESTER, 35 KGF/CM2, W/ PUMP
P3015-KPA	4184502	GAS DEADWEIGHT TESTER, 3500 KPA, NO PUMP
P3015-KPA-P	4184516	GAS DEADWEIGHT TESTER, 3500 KPA, W/ PUMP
P3015-MPA	4184525	GAS DEADWEIGHT TESTER, 3.5 MPA, NO PUMP
P3015-MPA-P	4184533	GAS DEADWEIGHT TESTER, 3.5 MPA, W/ PUMP
P3015-PSI	4184482	GAS DEADWEIGHT TESTER, 500 PSI, NO PUMP
P3015-PSI-P	4184494	GAS DEADWEIGHT TESTER, 500 PSI, W/ PUMP
P3022-INH2O	4184584	GAS DEADWEIGHT TESTER, DUAL VAC/PRESSURE 400 INH2O, NO PUMP
P3022-INH2O-P	4184591	GAS DEADWEIGHT TESTER, DUAL VAC/PRESSURE 400 INH2O, W/ PUMP
P3022-KPA	4184540	GAS DEADWEIGHT TESTER, DUAL VAC/PRESSURE 100 KPA, NO PUMP
P3022-KPA-P	4184557	GAS DEADWEIGHT TESTER, DUAL VAC/PRESSURE 100 KPA, W/ PUMP
P3022-MBAR	4184569	GAS DEADWEIGHT TESTER, DUAL VAC/PRESSURE 1000 MBAR, NO PUMP
P3022-MBAR-P	4184578	GAS DEADWEIGHT TESTER, DUAL VAC/PRESSURE 1000 MBAR, W/ PUMP
P3023-INH2O	4184656	GAS DEADWEIGHT TESTER, DUAL VAC/PRESSURE 800 INH2O, NO PUMP
P3023-INH2O-P	4184663	GAS DEADWEIGHT TESTER, DUAL VAC/PRESSURE 800 INH2O, W/ PUMP
P3023-KPA	4184600	GAS DEADWEIGHT TESTER, DUAL VAC/PRESSURE 200 KPA, NO PUMP
P3023-KPA-P	4184621	GAS DEADWEIGHT TESTER, DUAL VAC/PRESSURE 200 KPA, W/ PUMP
P3023-MBAR	4184639	GAS DEADWEIGHT TESTER, DUAL VAC/PRESSURE 2000 MBAR, NO PUMP
P3023-MBAR-P	4184642	GAS DEADWEIGHT TESTER, DUAL VAC/PRESSURE 2000 MBAR, W/ PUMP
P3025-BAR	4184674	GAS DEADWEIGHT TESTER, DUAL VAC/PRESSURE 35 BAR, NO PUMP
P3025-BAR-P	4184688	GAS DEADWEIGHT TESTER, DUAL VAC/PRESSURE 35 BAR, W/ PUMP
P3025-KGCM2	4184695	GAS DEADWEIGHT TESTER, DUAL VAC/PRESSURE 35 KGF/CM2, NO PUMP
P3025-KGCM2-P	4184707	GAS DEADWEIGHT TESTER, DUAL VAC/PRESSURE 35 KGF/CM2, W/ PUMP
P3025-KPA	4184734	GAS DEADWEIGHT TESTER, DUAL VAC/PRESSURE 3500 KPA, NO PUMP
P3025-KPA-P	4184741	GAS DEADWEIGHT TESTER, DUAL VAC/PRESSURE 3500 KPA, W/ PUMP
P3025-MPA	4184752	GAS DEADWEIGHT TESTER, DUAL VAC/PRESSURE 3.5 MPA, NO PUMP
P3025-MPA-P	4184765	GAS DEADWEIGHT TESTER, DUAL VAC/PRESSURE 3.5 MPA, W/ PUMP
P3025-PSI	4184718	GAS DEADWEIGHT TESTER, DUAL VAC/PRESSURE 500 PSI, NO PUMP
P3025-PSI-P	4184729	GAS DEADWEIGHT TESTER, DUAL VAC/PRESSURE 500 PSI, W/ PUMP
P3031-BAR	4184776	GAS DEADWEIGHT TESTER, LIQUID LUBRICATED, 70 BAR
P3031-KGCM2	4184783	GAS DEADWEIGHT TESTER, LIQUID LUBRICATED, 70 KGF/CM2
P3031-KPA	4184803	GAS DEADWEIGHT TESTER, LIQUID LUBRICATED, 7000 KPA
P3031-MPA	4184815	GAS DEADWEIGHT TESTER, LIQUID LUBRICATED, 7 MPA
P3031-PSI	4184790	GAS DEADWEIGHT TESTER, LIQUID LUBRICATED, 1000 PSI
P3032-BAR	4184826	GAS DEADWEIGHT TESTER, LIQUID LUBRICATED, 140 BAR
P3032-KGCM2	4184832	GAS DEADWEIGHT TESTER, LIQUID LUBRICATED, 140 KGF/CM2
P3032-KPA	4184859	GAS DEADWEIGHT TESTER, LIQUID LUBRICATED, 14K KPA
P3032-MPA	4184867	GAS DEADWEIGHT TESTER, LIQUID LUBRICATED, 14 MPA
P3032-PSI	4184844	GAS DEADWEIGHT TESTER, LIQUID LUBRICATED, 2000 PSI
P3111-BAR	4184880	OIL DEADWEIGHT TESTER, 35 BAR

Offer valid through December 31, 2016. Redemptions must be sent within 30 days of purchase.

Fluke Calibration Products Eligible for Accurate Power of Fluke Promotion

P3111-KGCM2	4184898	OIL DEADWEIGHT TESTER, 35 KGF/CM2
P3111-KPA	4184914	OIL DEADWEIGHT TESTER, 3500 KPA
P3111-MPA	4184923	OIL DEADWEIGHT TESTER, 3.5 MPA
P3111-PSI	4184906	OIL DEADWEIGHT TESTER, 500 PSI
P3112-BAR	4184945	OIL DEADWEIGHT TESTER, 140 BAR
P3112-KGCM2	4184950	OIL DEADWEIGHT TESTER, 140 KGF/CM2
P3112-MPA	4184977	OIL DEADWEIGHT TESTER, 14 MPA
P3112-PSI	4184961	OIL DEADWEIGHT TESTER, 2000 PSI
P3113-BAR	4184992	OIL DEADWEIGHT TESTER, 350 BAR
P3113-KGCM2	4185007	OIL DEADWEIGHT TESTER, 350 KGF/CM2
P3113-MPA	4185029	OIL DEADWEIGHT TESTER, 35 MPA
P3113-PSI	4185018	OIL DEADWEIGHT TESTER, 5000 PSI
P3114-BAR	4185041	OIL DEADWEIGHT TESTER, 700 BAR
P3114-KGCM2	4185052	OIL DEADWEIGHT TESTER, 700 KGF/CM2
P3114-MPA	4185076	OIL DEADWEIGHT TESTER, 70 MPA
P3114-PSI	4185065	OIL DEADWEIGHT TESTER, 10K PSI
P3115-BAR	4185090	OIL DEADWEIGHT TESTER, 1100 BAR
P3115-KGCM2	4185104	OIL DEADWEIGHT TESTER, 1100 KGF/CM2
P3115-MPA	4185128	OIL DEADWEIGHT TESTER, 110 MPA
P3115-PSI	4185119	OIL DEADWEIGHT TESTER, 16000 PSI
P3116-BAR	4185143	OIL DEADWEIGHT TESTER, 1400 BAR
P3116-KGCM2	4185155	OIL DEADWEIGHT TESTER, 1400 KGF/CM2
P3116-MPA	4185170	OIL DEADWEIGHT TESTER, 140 MPA
P3116-PSI	4185162	OIL DEADWEIGHT TESTER, 20K PSI
P3123-BAR	4185196	OIL DEADWEIGHT TESTER, DUAL RANGE, 350 BAR
P3123-KGCM2	4185205	OIL DEADWEIGHT TESTER, DUAL RANGE, 350 KGF/CM2
P3123-MPA	4185222	OIL DEADWEIGHT TESTER, DUAL RANGE, 35 MPA
P3123-PSI	4185210	OIL DEADWEIGHT TESTER, DUAL RANGE, 5000 PSI
P3124-BAR	4185246	OIL DEADWEIGHT TESTER, DUAL RANGE, 700 BAR
P3124-KGCM2	4185254	OIL DEADWEIGHT TESTER, DUAL RANGE, 700 KGF/CM2
P3124-MPA	4185279	OIL DEADWEIGHT TESTER, DUAL RANGE, 70 MPA
P3124-PSI	4185268	OIL DEADWEIGHT TESTER, DUAL RANGE, 10K PSI
P3125-BAR	4185302	OIL DEADWEIGHT TESTER, DUAL RANGE, 1100 BAR
P3125-KGCM2	4185316	OIL DEADWEIGHT TESTER, DUAL RANGE, 1100 KGF/CM2
P3125-MPA	4185333	OIL DEADWEIGHT TESTER, DUAL RANGE, 110 MPA
P3125-PSI	4185325	OIL DEADWEIGHT TESTER, DUAL RANGE, 16000 PSI
P3125XT-BAR	4378330	OIL DEADWEIGHT TESTER, DUAL RANGE, 1200 BAR
P3125XT-KGCM2	4378366	OIL DEADWEIGHT TESTER, DUAL RANGE, 1200 KGF/CM2
P3125XT-MPA	4378348	OIL DEADWEIGHT TESTER, DUAL RANGE, 120 MPA
P3211-BAR	4185357	WATER DEADWEIGHT TESTER, 35 BAR
P3211-KGCM2	4185369	WATER DEADWEIGHT TESTER, 35 KGF/CM2
P3211-KPA	4185384	WATER DEADWEIGHT TESTER, 3500 KPA
P3211-MPA	4185391	WATER DEADWEIGHT TESTER, 3.5 MPA
P3211-PSI	4185378	WATER DEADWEIGHT TESTER, 500 PSI
P3213-BAR	4185406	WATER DEADWEIGHT TESTER, 350 BAR
P3213-KGCM2	4185414	WATER DEADWEIGHT TESTER, 350 KGF/CM2
P3213-MPA	4185438	WATER DEADWEIGHT TESTER, 35 MPA
P3213-PSI	4185423	WATER DEADWEIGHT TESTER, 5000 PSI
P3214-BAR	4185445	WATER DEADWEIGHT TESTER, 700 BAR
P3214-KGCM2	4185450	WATER DEADWEIGHT TESTER, 700 KGF/CM2
P3214-MPA	4185477	WATER DEADWEIGHT TESTER, 70 MPA
P3214-PSI	4185461	WATER DEADWEIGHT TESTER, 10K PSI
P3223-BAR	4185489	WATER DEADWEIGHT TESTER, DUAL RANGE, 350 BAR
P3223-KGCM2	4185492	WATER DEADWEIGHT TESTER, DUAL RANGE, 350 KGF/CM2
P3223-MPA	4185511	WATER DEADWEIGHT TESTER, DUAL RANGE, 35 MPA
P3223-PSI	4185509	WATER DEADWEIGHT TESTER, DUAL RANGE, 5000 PSI
P3224-BAR	4185527	WATER DEADWEIGHT TESTER, DUAL RANGE, 700 BAR
P3224-KGCM2	4185530	WATER DEADWEIGHT TESTER, DUAL RANGE, 700 KGF/CM2
P3224-MPA	4185553	WATER DEADWEIGHT TESTER, DUAL RANGE, 70 MPA
P3224-PSI	4185548	WATER DEADWEIGHT TESTER, DUAL RANGE, 10K PSI
P3800C	3964127	HIGH PRESSURE COMPARISON TEST PUMP
P3830-BAR	4185566	OIL DEADWEIGHT TESTER, 2000 BAR
P3830-MPA	4185582	OIL DEADWEIGHT TESTER, 200 MPA

Offer valid through December 31, 2016. Redemptions must be sent within 30 days of purchase.

Fluke Calibration Products Eligible for Accurate Power of Fluke Promotion

P3830-PSI	4185575	OIL DEADWEIGHT TESTER, 30K PSI
P3840-BAR	4185594	OIL DEADWEIGHT TESTER, 2600 BAR
P3840-MPA	4185613	OIL DEADWEIGHT TESTER, 260 MPA
P3840-PSI	4185608	OIL DEADWEIGHT TESTER, 40K PSI
P3860-BAR	4185624	OIL DEADWEIGHT TESTER, 4000 BAR
P3860-MPA	4185649	OIL DEADWEIGHT TESTER, 400 MPA
P3860-PSI	4185636	OIL DEADWEIGHT TESTER, 60K PSI
P5510/14-2700G-4	4341774	P5510/P5514 PRESSURE CALIBRATOR, WITH 4 GAUGES
P5510/14-2700G-4/C	4341813	P5510/P5514 PRESSURE CALIBRATOR, WITH 4 GAUGES ACCREDITED
P5510/14-2700G-6	4341756	P5510/P5514 PRESSURE CALIBRATOR, WITH 6 GAUGES
P5510/14-2700G-6/C	4341795	P5510/P5514 PRESSURE CALIBRATOR, WITH 6 GAUGES ACCREDITED
P5510/15-2700G-4	4341788	P5510/P5515 PRESSURE CALIBRATOR, WITH 4 GAUGES
P5510/15-2700G-4/C	4341824	P5510/P5515 PRESSURE CALIBRATOR, WITH 4 GAUGES ACCREDITED
P5510/15-2700G-6	4341763	P5510/P5515 PRESSURE CALIBRATOR, WITH 6 GAUGES
P5510/15-2700G-6/C	4341808	P5510/P5515 PRESSURE CALIBRATOR, WITH 6 GAUGES ACCREDITED
P5510-2700G-1	4341589	P5510 PNEUMATIC CALIBRATOR, 2 MPA (300 PSI), 1 GAUGE
P5510-2700G-1/C	4341668	P5510 PNEUMATIC CALIBRATOR, 2 MPA (300 PSI), 1 GAUGE ACCREDITED
P5510-2700G-3	4341592	P5510 PNEUMATIC CALIBRATOR, 2 MPA (300 PSI), 3 GAUGES
P5510-2700G-3/C	4341679	P5510 PNEUMATIC CALIBRATOR, 2 MPA (300 PSI), 3 GAUGES ACCREDITED
P5510-2M	4185651	PNEUMATIC TEST PUMP, VACUUM TO 2 MPA (300 PSI)
P5513-20M	4185660	PNEUMATIC TEST PUMP, VACUUM TO 20 MPA (3000 PSI)
P5513-2700G-1	4341605	P5513 PNEUMATIC CALIBRATOR, 20 MPA(3000 PSI), 1 GAUGE
P5513-2700G-1/C	4341687	P5513 PNEUMATIC CALIBRATOR, 20 MPA(3000 PSI), 1 GAUGE ACCREDITED
P5513-2700G-3	4341610	P5513 PNEUMATIC CALIBRATOR, 20 MPA (3000 PSI), 3 GAUGES
P5513-2700G-3/C	4341693	P5513 PNEUMATIC CALIBRATOR, 20MPA(3000 PSI), 3 GAUGES ACCREDITED
P5514-2700G-1	4341622	P5514 HYDRAULIC CALIBRATOR, 70 MPA (10 000 PSI), 1 GAUGE
P5514-2700G-1/C	4341717	P5514 HYDRAULIC CALIBRATOR, 70 MPA (10K PSI), 1 GAUGE ACCREDITED
P5514-2700G-3	4341631	P5514 HYDRAULIC CALIBRATOR, 70 MPA (10 000 PSI), 3 GAUGES
P5514-2700G-3/C	4341721	P5514 HYDRAULIC CALIBRATOR, 70 MPA(10K PSI), 3 GAUGES ACCREDITED
P5514-70M	4185672	HYDRAULIC TEST PUMP, 70 MPA (10K PSI)
P5514-70M-EP	4185685	HYDRAULIC TEST PUMP, 70 MPA (10K PSI), EP SEALS
P5515-140M	4185697	HYDRAULIC TEST PUMP, 140 MPA (20K PSI)
P5515-140M-EP	4185703	HYDRAULIC TEST PUMP, 140 MPA (20K PSI), EP SEALS
P5515-2700G-1	4341646	P5515 HYDRAULIC CALIBRATOR, 70 MPA (10 000 PSI), 1 GAUGE
P5515-2700G-1/C	4341739	P5515 HYDRAULIC CALIBRATOR, 70 MPA(10K PSI), 1 GAUGE ACCREDITED
P5515-2700G-3	4341654	P5515 HYDRAULIC CALIBRATOR, 70 MPA (10 000 PSI), 3 GAUGES
P5515-2700G-3/C	4341742	P5515 HYDRAULIC CALIBRATOR, 70 MPA(10K PSI), 3 GAUGES ACCREDITED
P5521-70M	4185715	LIQUID TO LIQUID SEPARATOR, 70 MPA (10K PSI)
P5522-50M	4185726	LIQUID TO LIQUID SEPARATOR, 50 MPA (7000 PSI), SKYDROL USE
P5523-20M	4185732	LIQUID TO GAS INTERFACE, 20 MPA (3000 PSI)
P5531-3.5M	4185744	DIRT/MOISTURE TRAP, 3.5 MPA (500 PSI)
P5532-20M	4185759	DIRT/MOISTURE TRAP, 20 MPA (3000 PSI)
P5540	3875928	ADAPTER SET - METRIC
P5541	3875937	ADAPTER SET - BSP
P5542	3875943	ADAPTER SET - NPT
P5543	3875955	ANGLE ADAPTER
P5544-STD	4185767	TWO GAUGE STAND, P3000 STD ADAPTORS
P5551	3885659	POINTER REMOVER / PUNCH
PIDT600-2	3963058	DIRT & MOISTURE TRAP 1/8 NPT 20 BAR/300 PSI
PIDT600-4	3948589	DIRT & MOISTURE TRAP 1/8 NPT
PIDT600-8	3985066	TRAP 1/4 BSP 210 BAR/3000 PSI
PIDT600-9	3948605	DIRT & MOISTURE TRAP 1/4 NPT 210 BAR/3000 PSI
PK-P3000-ADPTR-STD	4185780	ADAPTOR SET, P3000 STANDARD
PPA9159-CAL	3886164	INCREMENTAL WEIGHTS
PPA9608-CAL	3886906	WEIGHTS GROUP - H* [PSI] [INCREMENTAL] CALD
PRESSCAL	4185771	PRESSCAL SOFTWARE (IMPROVED ACCURACY)
FLK-789/773 BU	4740387	FLUKE - 789 AND 773 BUNDLE PACKAGE
FLK-789/IR3000 BU	4740393	FLUKE-789 AND IR3000FC BUNDLE PACKAGE
FLUKE-719 100G	3315344	ELECTRIC PRESSURE CALIBRATOR, 100 PSI, 7 BAR
FLUKE-719 30G	3315332	ELECTRIC PRESSURE CALIBRATOR, 30 PSI, 2 BAR
FLUKE-719PRO-150G	4353229	ELECTRIC PRESSURE CALIBRATOR, 150 PSI
FLUKE-719PRO-300G	4353234	ELECTRIC PRESSURE CALIBRATOR, 300 PSIG
FLUKE-719PRO-30G	4353218	ELECTRIC PRESSURE CALIBRATOR, 30 PSIG

Offer valid through December 31, 2016. Redemptions must be sent within 30 days of purchase.

Fluke Calibration Products Eligible for Accurate Power of Fluke Promotion

FLUKE-71X	3345825	HOSE KIT ACCESSORY
FLUKE-71X-TRAP	4380747	TRAP, LIQUID DIRT, GENERIC
FLUKE-720RTD	4366669	RTD PROBE FOR 721 AND 719PRO
FLUKE-720URTD	4382695	UNIVERSAL RTD ADAPTER, FLUKE -719PRO AND FLUKE-721
FLUKE-721-1601	4353241	DUAL SENSOR PRESSURE CALIBRATOR, 16 PSIG, 100 PSIG
FLUKE-721-1603	4353283	DUAL SENSOR PRESSURE CALIBRATOR, 16 PSIG, 300 PSIG
FLUKE-721-1605	4353327	DUAL SENSOR PRESSURE CALIBRATOR, 16 PSIG, 500 PSIG
FLUKE-721-1610	4353366	DUAL SENSOR PRESSURE CALIBRATOR, 16 PSIG, 1000 PSIG
FLUKE-721-1615	4353401	DUAL SENSOR PRESSURE CALIBRATOR, 16 PSIG, 1500 PSIG
FLUKE-721-1630	4353447	DUAL SENSOR PRESSURE CALIBRATOR, 16 PSIG, 3000 PSIG
FLUKE-721-1650	4353486	DUAL SENSOR PRESSURE CALIBRATOR, 16 PSIG, 5000 PSIG
FLUKE-721-3601	4353252	DUAL SENSOR PRESSURE CALIBRATOR, 36 PSIG, 100 PSIG
FLUKE-721-3603	4353290	DUAL SENSOR PRESSURE CALIBRATOR, 36 PSIG, 300 PSIG
FLUKE-721-3605	4353330	DUAL SENSOR PRESSURE CALIBRATOR, 36 PSIG, 500 PSIG
FLUKE-721-3610	4353375	DUAL SENSOR PRESSURE CALIBRATOR, 36 PSIG, 1000 PSIG
FLUKE-721-3615	4353412	DUAL SENSOR PRESSURE CALIBRATOR, 36 PSIG, 1500 PSIG
FLUKE-721-3630	4353458	DUAL SENSOR PRESSURE CALIBRATOR, 36 PSIG, 3000 PSIG
FLUKE-721-3650	4353499	DUAL SENSOR PRESSURE CALIBRATOR, 36 PSIG, 5000 PSIG
FLUKE-721EX-1601	4353265	DUAL SENSOR PRESSURE CALIBRATOR, 16 PSIG, 100 PSIG
FLUKE-721EX-1603	4353309	DUAL SENSOR PRESSURE CALIBRATOR, 16 PSIG, 300 PSIG
FLUKE-721EX-1605	4353348	DUAL SENSOR PRESSURE CALIBRATOR, 16 PSIG, 500 PSIG
FLUKE-721EX-1610	4353382	DUAL SENSOR PRESSURE CALIBRATOR, 16 PSIG, 1000 PSIG
FLUKE-721EX-1615	4353420	DUAL SENSOR PRESSURE CALIBRATOR, 16 PSIG, 1500 PSIG
FLUKE-721EX-1630	4353464	DUAL SENSOR PRESSURE CALIBRATOR, 16 PSIG, 3000 PSIG
FLUKE-721EX-1650	4353506	DUAL SENSOR PRESSURE CALIBRATOR, 16 PSIG, 5000 PSIG
FLUKE-721EX-3601	4353276	DUAL SENSOR PRESSURE CALIBRATOR, 36 PSIG, 100 PSIG
FLUKE-721EX-3603	4353311	DUAL SENSOR PRESSURE CALIBRATOR, 36 PSIG, 300 PSIG
FLUKE-721EX-3605	4353353	DUAL SENSOR PRESSURE CALIBRATOR, 36 PSIG, 500 PSIG
FLUKE-721EX-3610	4353394	DUAL SENSOR PRESSURE CALIBRATOR, 36 PSIG, 1000 PSIG
FLUKE-721EX-3615	4353435	DUAL SENSOR PRESSURE CALIBRATOR, 36 PSIG, 1500 PSIG
FLUKE-721EX-3630	4353473	DUAL SENSOR PRESSURE CALIBRATOR, 36 PSIG, 3000 PSIG
FLUKE-721EX-3650	4353514	DUAL SENSOR PRESSURE CALIBRATOR, 36 PSIG, 5000 PSIG
FLUKE-726	2452080	PRECISION MULTIFUNCTION CALIBRATOR
FLUKE-753	3977641	DOCUMENTING PROCESS CALIBRATOR, NON BUS
FLUKE-754	3405771	DOCUMENTING PROCESS CALIBRATOR
FLUKE-754/750SW BU	4465547	FLUKE-754 DPC AND 750SW DPCTRACK2 BUNDLE PACKAGE
2383	2761737	ADAPTER, USB SERIAL
9930	3623872	SOFTWARE, INTERFACE-IT
9933	1658726	SOFTWARE, TABLEWARE
9940	3623885	SOFTWARE, IO TOOLKIT
9934-M	1658732	SOFTWARE, LOGWARE, 1-CHAN, MULTI USER
9934-S	1658744	SOFTWARE, LOGWARE, 1-CHAN, SINGLE USER
9935-M	1658759	SOFTWARE, LOGWARE II, 2+-CHAN, MULTI USER
9935-S	1658767	SOFTWARE, LOGWARE II, 2+-CHAN, SINGLE USER
9936A	2724086	SOFTWARE, LOGWARE III (SINGLE-PC LICENSE)
9936A-L1	2724099	LICENSE, LOGWARE III, 1-PACK
9936A-L10	2724110	LICENSE, LOGWARE III, 10-PACK
9936A-L5	2724105	LICENSE, LOGWARE III, 5-PACK
9936A-LST	2724122	LICENSE, LOGWARE III, SITE
9939-CB	3981362	SOFTWARE, MET/TEMP-CB
9939-CM	3981370	SOFTWARE, MET/TEMP-CM
LIC-9938	2088942	LICENSE, MET/TEMP II TO MET/TRACK 7.0
TQAERO	4725926	SOFTWARE, TQAERO
TQSOFT-IQ/OQ	4725915	SOFTWARE, TQSOFT, W/ IQ/OQ
TQSOFT-IQ/OQ/D	4725944	SOFTWARE, TQSOFT, W/ IQ/OQ
VAL-BNDR-TQS	4725932	VALIDATION REF BINDER FOR TQSOFT, (CD)
VAL-BNDR-TQS/D	4725967	VALIDATION REF BINDER FOR TQSOFT, (CD)
2083	1649963	EXTENDER, TANK (6102, 7102)
2085	1649988	COVER, PLASTIC BLANK ACCESS (7103)
2370	1650431	CABLE, RS-232 (1521,1522)
2371	1650446	CONNECTOR, INFO-CON
2505	1650686	CONNECTOR, SPARE DIN, 5 PIN (1502-4)
2601	1650896	CASE, PROBE CARRYING

Offer valid through December 31, 2016. Redemptions must be sent within 30 days of purchase.

Fluke Calibration Products Eligible for Accurate Power of Fluke Promotion

2609	2788701	CASE, LONG PROBE CARRYING
2628	2112289	CABLE, 25 FT. EXTENSION, 1620-X
2629	2106048	CABLE, 50 FT. EXTENSION, 1620-X
3320	1648457	BAR, 7/16IN DIA X 2.00 MAGNETIC STIR
5577	2100337	THERMOMETER, P655 HAND-HELD
9300	1658509	CASE, RUGGED CARRYING (9100)
9301	1658511	CASE, RUGGED CARRYING
9308	1658575	CASE, HARD CARRYING
9310	1658594	CASE, MICRO-BATH CARRYING (6102)
9311	1658608	CASE, MICRO-BATH CARRYING (7102)
9315	1658636	CASE, CARRYING (9150)
9316	1658649	CASE, CARRYING (9103)
9317	1658651	CASE, MICRO-BATH CARRYING (7103)
9322	1658685	CASE, CARRYING (1529 AND PROBES)
9326	2100355	CASE, CARRYING (5577 AND 2-300 MM PROBES)
9328	2106066	CASE, CARRYING, 1620-X
1502A-156	1648927	THERMOMETER, TWEENER, 110V 50/60HZ
1504-156	1648966	THERMOMETER, THERMISTOR, 110V 50/60HZ
1523-156	3376516	THERMOMETER, HANDHELD, 1 CHANNEL
1523-CAL	3376688	CALIBRATION, NVLAP ACCREDITED
1523-CASE	3376533	CASE, 1523/1524 READOUT AND PROBE CARRYING
1523-P1-156	3376540	BUNDLE, 1523 W/CASE,5616,LEMO TO TC ADAPTER
1523-P2-156	3376569	BUNDLE, 1523 W/CASE,5628,LEMO TO TC ADAPTER
1523-P3-156	3376584	BUNDLE, 1523 W/CASE,5627A,LEMO TO TC ADAPTER
1524-156	3376600	THERMOMETER, HANDHELD, 2 CH DATA LOGGER
1524-CAL	3376695	CALIBRATION, NVLAP ACCREDITED
1524-P1-156	3376621	BUNDLE, 1524 W/CASE,5616,LEMO TO TC ADAPTER
1524-P2-156	3376642	BUNDLE, 1524 W/CASE,5628,LEMO TO TC ADAPTER
1524-P3-156	3376663	BUNDLE, 1524 W/CASE,5627A,LEMO TO TC ADAPTER
1529-156	1672258	THERMOMETER,CHUB-E4,2-PRT,2-TC
1529-R-156	1672247	THERMOMETER,CHUB-E4,4-PRT/THERMISTOR
1529-T-156	1672235	THERMOMETER,CHUB-E4,4-TC INPUTS
1551A-12	3624149	THERMOMETER, FIXED RTD, -50 TO 160C, 1/4X12
1551A-12-DL	3936037	THERMOMETER,RTD,-50 TO 160C, 1/4X12 W/DATALOG
1551A-20	3935995	THERMOMETER, FIXED RTD, -50 TO 160C, 1/4X20
1551A-20-DL	3936055	THERMOMETER,RTD,-50 TO 160C, 1/4X20 W/DATALOG
1551A-9	3624136	THERMOMETER, FIXED RTD, -50 TO 160C, 3/16X9
1551A-9-DL	3936019	THERMOMETER,RTD,-50 TO 160C, 3/16X9 W/DATALOG
1551-CASE	3624160	CASE, 1551-2, CARRYING
1551-CBL	3936096	CABLE, RS-232, 155X
1552A-12	3624151	THERMOMETER, FIXED PRT, -80 TO 300C, 1/4X12
1552A-12-DL	3936070	THERMOMETER,PRT,-80 TO 300C, 1/4X12 W/DATALOG
1586/DS-CASE	4406724	CASE, CARRYING, 1586A AND 1586-2588
1586-2586	4409820	MODULE (ONLY), HI-CAPACITY MODULE W/OUT RELAY CARD
1586-2586/C	4410748	MODULE (ONLY), HI-CAPACITY MODULE W/OUT RELAY CARD, ACCRED CAL
1586-2586-KIT	4409835	MODULE, HI-CAPACITY MODULE WITH RELAY CARD
1586-2586-KIT/C	4410753	MODULE, HI-CAPACITY MODULE WITH RELAY CARD, ACCRED CAL
1586-2586-RLY	4410113	RELAY CARD, HI-CAPACITY MODULE
1586-2588	4409847	MODULE (ONLY), DAQ-STAQ MODULE, W/OUT ADAPTER CARD
1586-2588/C	4410766	MODULE (ONLY), DAQ-STAQ MODULE, W/OUT ADAPTER CARD, ACCRED CAL
1586-2588-ADP	4409858	ADAPTER CARD (ONLY), DAQ-STAQ MODULE, 1586A
1586-2588-CBL	4410465	CABLE, DAQ-STAQ MODULE, CNTRL/INPUT
1586-2588-KIT	4409864	MODULE, DAQ-STAQ WITH ADAPTER CARD & CABLE
1586-2588-KIT/C	4410775	MODULE, DAQ-STAQ WITH ADAPTER CARD & CABLE, ACCRED CAL
1586A 120	4409886	SUPER-DAQ, MAINFRAME ONLY, 120 V
1586A 120/C	4377390	SUPER-DAQ, MAINFRAME ONLY, 120 V, ACCREDITED CAL
1586A/1DS 120	4409921	SUPER-DAQ, 1 DAQ-STAQ MODULE, 120 V
1586A/1DS 120/C	4377579	SUPER-DAQ, 1 DAQ-STAQ MODULE, 120V, ACCREDITED CAL
1586A/1HC 120	4409963	SUPER-DAQ, 1 HI-CAPACITY MODULE, 120 V
1586A/1HC 120/C	4384181	SUPER-DAQ, 1 HI-CAPACITY MODULE, 120V, ACCREDITED CAL
1586A/2DS 120	4410006	SUPER-DAQ, 2 DAQ-STAQ MODULES, 120 V
1586A/2DS 120/C	4377762	SUPER-DAQ, 2 DAQ-STAQ MODULES, 120V, ACCREDITED CAL
1586A/2HC 120	4410045	SUPER-DAQ, 2 HI-CAPACITY MODULES, 120 V

Offer valid through December 31, 2016. Redemptions must be sent within 30 days of purchase.

Fluke Calibration Products Eligible for Accurate Power of Fluke Promotion

1586A/2HC 120/C	4384369	2 HI-CAPACITY MODULES, 100V, ACCREDITED CAL
1586A/DS-HC 120	4410089	SUPER-DAQ, 1 INT/1 EXT MODULE, 120 V
1586A/DSHC 120/C	4384651	SUPER-DAQ, 1 INT/1 EXT MODULE, 120V, ACCREDITED CAL
1586-CASE	4406713	CASE, CARRYING, 1586A
1620A-BASE-156	2761755	BASE, THERMO-HYGROMETER, DEWK
1620A-H-156	2723978	THERMO-HYGROMETER, DEWK, HIGH ACCURACY
1620A-S-156	2723991	THERMO-HYGROMETER, DEWK, STANDARD
1621A-H-156	2724012	KIT, THERMO-HYGROMETER, DEWK, HIGH ACCURACY
1621A-S-156	2724035	KIT, THERMO-HYGROMETER, DEWK, STANDARD
1622A-H-156	2761770	KIT, USB WIRELESS, DEWK, HIGH ACCURACY
1622A-S-156	2761796	KIT, USB WIRE-LESS, DEWK, STANDARD
1623A-H-156	3806985	KIT, DEWK,HIGH ACCURACY (50FT CABLE)
1623A-S-156	3806960	KIT, DEWK,STANDARD (50FT CABLE)
2082-M	1649942	COVER, METAL BLANK ACCESS (6102)
2082-P	1649956	COVER, PLASTIC BLANK ACCESS (7102)
2361-156	2085434	ADAPTER, SPARE AC, 12V (1521/1522), 110V
2362-156	2085452	ADAPTER, SPARE AC, 15V (1529), 110V
2373-DIN	3100316	ADAPTER, RND INFO-CON TO SPADE LUG
2373-L21	3476835	ADAPTER, LEMO TO 1521/1522 INFO-CON
2373-LPRT	3376707	ADAPTER, LEMO TO MINI GRABBERS (PRT)
2373-LSP	3376718	ADAPTER, FEMALE LEMO TO SPADE LUG
2373-LTC	3376729	ADAPTER, LEMO TO UNIVERSAL TC (TC)
2383-1	3835068	CABLE, SERIAL TO USB CONVERTER
2384-P	3376734	SMART CONNECTOR, PRT (GRAY CAP)
2389-P	4146454	CABLE, PROBE EXT, FM LEMO TO ML LEMO (50 FT)
2523-156	3463870	ISOLATOR,RS232 OPTICAL 12VDC (1523/1524), 110V
2626-H	2105993	PROBE, THERMO-HYGROMETER SPARE, 1620-H
2626-S	2106009	PROBE, THERMO-HYGROMETER SPARE, 1620-S
2627-H	2106011	KIT, THERMO-HYGROMETER SPARE PROBE, 1620-H
2627-S	2106027	KIT, THERMO-HYGROMETER SPARE PROBE, 1620-S
2630H	2111586	BRACKET, PROBE WALL MOUNT
2633-232	2724064	RECEIVER, RS232 TO WIRELESS (1620A)
2633-RF	2724073	OPTION, FACTORY INSTALL WIRELESS CHIP (1620A)
2633-USB	2724058	RECEIVER, USB TO WIRELESS (1620A)
3102-0	1650985	INSERT, AL BLANK (9102, 9009)
3102-1	1650997	INSERT, AL 1/16IN (9102, 9009)
3102-2	1651002	INSERT, AL 1/8IN (9102, 9009)
3102-3	1651016	INSERT, AL 3/16IN (9102, 9009)
3102-4	1651025	INSERT, AL 1/4IN (9102, 9009)
3102-5	1651033	INSERT, AL 5/16IN (9102, 9009)
3102-6	1651040	INSERT, AL 3/8IN (9102, 9009)
3102-7	1651057	INSERT, AL 7/16IN (9102, 9009)
3102-8	1651069	INSERT, AL 5/32IN (9102, 9009)
3103-1	1651078	INSERT, BLANK (9103)
3103-2	1651084	INSERT, A W/ MISC HOLES (9103)
3103-3	1651091	INSERT, B W/ COMPARISON HOLES (9103)
3103-4	1651103	INSERT, C W/ 6 EA .25IN HOLES (9103)
3103-6	1884839	INSERT, D , 9011/9103
3103-Y	2644412	INSERT, CUSTOM, 9011/9103
3140-1	1651579	INSERT, BLANK, RING (9140)
3140-2	1651587	INSERT, A W/ MISC HOLES, RING (9140)
3140-3	1651593	INSERT, B W/ CMPRSN HOLES (9140)
3140-4	1651606	INSERT, C W/ 6 0.25IN HOLES, RING (9140)
3140-6	1884863	INSERT, 9140, D, W/ MISC HOLES, RING
3141-1	1651614	INSERT, AL-BRNZ BLANK (9141)
3141-2	1651623	INSERT, A AL-BRNZ W/ MISC HOLES (9141)
3141-3	1651638	INSERT, B AL-BRNZ W/ CMPRSN HOLES (9141)
3141-4	1651645	INSERT, C AL-BRNZ W/ 6 0.25IN HOLES (9141)
3141-6	1884874	INSERT, 9141, D , AL-BRNZ W/ MISC HOLES
3150-2	1651650	INSERT, A ALUMINA W/ MISC HOLES (9150)
3150-3	1651661	INSERT, B ALUMINA W/ COMPRSN HOLES (9150)
3150-4	1651677	INSERT, C ALUMINA W/ 6 .25IN HOLES (9150)

Offer valid through December 31, 2016. Redemptions must be sent within 30 days of purchase.

Fluke Calibration Products Eligible for Accurate Power of Fluke Promotion

3150-6	2085476	INSERT, 9150-D ALUMINA W/ 6 METRIC HOLES
4180-156	3109516	IR CALIBRATOR,152 MM (6IN), -15 TO 120C,115V
4180-APRT	3277383	APERTURE, IR INSTRUMENT
4180-CASE	3109591	CASE, CARRYING, 4180/4181
4180-DCAS	3186636	CASE, 4180-81, CARRYING, W/WHEELS
4180-PURGEBOX	4034585	PURGE-BOX, PLEXIGLASS
4181-156	3109557	IR CALIBRATOR, 152 MM (6IN), 35 TO 500C,115V
5010-1L	2430005	FLUID, SILICONE OIL 200.05, 1 L (0.26 US GAL)
5013-18.9L	2430087	FLUID, SILICONE OIL 200.20, 18.9 L (5 US GAL)
5013-1L	2430093	FLUID, SILICONE OIL 200.20, 1 L (0.26 US GAL)
5013-3.8L	2430101	FLUID, SILICONE OIL 200.20, 3.8 L (1 US GAL)
5315-001	2100297	PROBE, IMMERSION, -100 TO 135C, 150 X 3 MM
5315-002	2100304	PROBE, IMMERSION, -100 TO 135C, 300 X 3 MM
5315-003	2100319	PROBE, IMMERSION, -100 TO 135C, 300 X 6 MM
5315-005	2100328	BATTERY, IS-APPROVED SPARE
5606-50-A	3622827	PROBE, IMMERSION PRT, 50MM, -200 TO 160C, W/O CAL
5606-50-B	3622830	PROBE, IMMERSION PRT, 50MM, -200 TO 160C
5606-50-D	3622848	PROBE, IMMERSION PRT, 50MM, -200 TO 160C
5606-50-G	3622853	PROBE, IMMERSION PRT, 50MM, -200 TO 160C
5606-50-I	3622866	PROBE, IMMERSION PRT, 50MM, -200 TO 160C
5606-50-J	3622875	PROBE, IMMERSION PRT, 50MM, -200 TO 160C
5606-50-L	3622882	PROBE, IMMERSION PRT, 50MM, -200 TO 160C
5606-50-M	3622894	PROBE, IMMERSION PRT, 50MM, -200 TO 160C
5606-50-P	3622907	PROBE, IMMERSION PRT, 50MM, -200 TO 160C
5606-50-S	3622918	PROBE, IMMERSION PRT, 50MM, -200 TO 160C
5608-12-A	4323692	PROBE, SECON. PRT, 100 OHM (1/8 X 12 INCH)
5608-12-B	3057043	PROBE, SECON. PRT, 100 OHM (1/8 x 12 INCH)
5608-12-D	3057055	PROBE, SECON. PRT, 100 OHM (1/8 X 12 INCH)
5608-12-G	3057062	PROBE, SECON. PRT, 100 OHM (1/8 X 12 INCH)
5608-12-I	3057070	PROBE, SECON. PRT, 100 OHM (1/8 X 12 INCH)
5608-12-J	3057081	PROBE, SECON. PRT, 100 OHM (1/8 X 12 INCH)
5608-12-L	3057096	PROBE, SECON. PRT, 100 OHM (1/8 X 12 INCH)
5608-12-M	3057107	PROBE, SECON. PRT, 100 OHM (1/8 X 12 INCH)
5608-12-P	3376752	PROBE, SECON. PRT, 100 OHM (1/8 X 12 INCH)
5608-12-S	3057118	PROBE, SECON. PRT, 100 OHM (1/8 X 12 INCH)
5608-9-B	3057129	PROBE, SECON. PRT, 100 OHM (1/8 X 9 INCH)
5608-9-D	3057134	PROBE, SECON. PRT, 100 OHM (1/8 X 9 INCH)
5608-9-G	3057141	PROBE, SECON. PRT, 100 OHM (1/8 X 9 INCH)
5608-9-I	3057152	PROBE, SECON. PRT, 100 OHM (1/8 X 9 INCH)
5608-9-J	3057165	PROBE, SECON. PRT, 100 OHM (1/8 X 9 INCH)
5608-9-L	3057176	PROBE, SECON. PRT, 100 OHM (1/8 X 9 INCH)
5608-9-M	3057183	PROBE, SECON. PRT, 100 OHM (1/8 X 9 INCH)
5608-9-P	3376765	PROBE, SECON. PRT, 100 OHM (1/8 X 9 INCH)
5608-9-S	3057190	PROBE, SECON. PRT, 100 OHM (1/8 X 9 INCH)
5609-12-A	3100973	PROBE, SECON. PRT, 100 OHM (1/4 X 12 INCH)
5609-12-B	3056569	PROBE, SECON. PRT, 100 OHM (1/4 X 12 INCH)
5609-12-D	3056578	PROBE, SECON. PRT, 100 OHM (1/4 X 12 INCH)
5609-12-G	3056584	PROBE, SECON. PRT, 100 OHM (1/4 X 12 INCH)
5609-12-I	3056591	PROBE, SECON. PRT, 100 OHM (1/4 X 12 INCH)
5609-12-J	3056600	PROBE, SECON. PRT, 100 OHM (1/4 X 12 INCH)
5609-12-L	3056617	PROBE, SECON. PRT, 100 OHM (1/4 X 12 INCH)
5609-12-M	3056621	PROBE, SECON. PRT, 100 OHM (1/4 X 12 INCH)
5609-12-P	3376776	PROBE, SECON. PRT, 100 OHM (1/4 X 12 INCH)
5609-12-S	3056639	PROBE, SECON. PRT, 100 OHM (1/4 X 12 INCH)
5609-15-A	3100986	PROBE, SECON. PRT, 100 OHM (1/4 X 12 INCH)
5609-15-B	3056642	PROBE, SECON. PRT, 100 OHM (1/4 X 15 INCH)
5609-15-D	3056656	PROBE, SECON. PRT, 100 OHM (1/4 X 15 INCH)
5609-15-G	3056663	PROBE, SECON. PRT, 100 OHM (1/4 X 15 INCH)
5609-15-I	3056674	PROBE, SECON. PRT, 100 OHM (1/4 X 15 INCH)
5609-15-J	3056688	PROBE, SECON. PRT, 100 OHM (1/4 X 15 INCH)
5609-15-L	3056695	PROBE, SECON. PRT, 100 OHM (1/4 X 15 INCH)
5609-15-M	3056707	PROBE, SECON. PRT, 100 OHM (1/4 X 15 INCH)
5609-15-P	3376783	PROBE, SECON. PRT, 100 OHM (1/4 X 15 INCH)

Offer valid through December 31, 2016. Redemptions must be sent within 30 days of purchase.

Fluke Calibration Products Eligible for Accurate Power of Fluke Promotion

5609-15-S	3056718	PROBE, SECON. PRT, 100 OHM (1/4 X 15 INCH)
5609-20-A	3100999	PROBE, SECON. PRT, 100 OHM (1/4 X 20 INCH)
5609-20-B	3056729	PROBE, SECON. PRT, 100 OHM (1/4 X 20 INCH)
5609-20-D	3056734	PROBE, SECON. PRT, 100 OHM (1/4 X 20 INCH)
5609-20-G	3056741	PROBE, SECON. PRT, 100 OHM (1/4 X 20 INCH)
5609-20-I	3056752	PROBE, SECON. PRT, 100 OHM (1/4 X 20 INCH)
5609-20-J	3056765	PROBE, SECON. PRT, 100 OHM (1/4 X 20 INCH)
5609-20-L	3056776	PROBE, SECON. PRT, 100 OHM (1/4 X 20 INCH)
5609-20-M	3056783	PROBE, SECON. PRT, 100 OHM (1/4 X 20 INCH)
5609-20-P	3376790	PROBE, SECON. PRT, 100 OHM (1/4 X 20 INCH)
5609-20-S	3056790	PROBE, SECON. PRT, 100 OHM (1/4 X 20 INCH)
5609-300-A	3561562	PROBE, SECON. PRT, 100 OHM (6 X 300 MM)
5609-300-B	3056803	PROBE, SECON. PRT, 100 OHM (6 X 300 MM)
5609-300-D	3056815	PROBE, SECON. PRT, 100 OHM (6 X 300 MM)
5609-300-G	3056826	PROBE, SECON. PRT, 100 OHM (6 X 300 MM)
5609-300-I	3056832	PROBE, SECON. PRT, 100 OHM (6 X 300 MM)
5609-300-J	3056844	PROBE, SECON. PRT, 100 OHM (6 X 300 MM)
5609-300-L	3056859	PROBE, SECON. PRT, 100 OHM (6 X 300 MM)
5609-300-M	3056867	PROBE, SECON. PRT, 100 OHM (6 X 300 MM)
5609-300-P	3376803	PROBE, SECON. PRT, 100 OHM (6 X 300 MM)
5609-300-S	3056871	PROBE, SECON. PRT, 100 OHM (6 X 300 MM)
5609-400-A	3561570	PROBE, SECON. PRT, 100 OHM (6 X 400 MM)
5609-400-B	3056880	PROBE, SECON. PRT, 100 OHM (6 X 400 MM)
5609-400-D	3056898	PROBE, SECON. PRT, 100 OHM (6 X 400 MM)
5609-400-G	3056906	PROBE, SECON. PRT, 100 OHM (6 X 400 MM)
5609-400-I	3056914	PROBE, SECON. PRT, 100 OHM (6 X 400 MM)
5609-400-J	3056923	PROBE, SECON. PRT, 100 OHM (6 X 400 MM)
5609-400-L	3056938	PROBE, SECON. PRT, 100 OHM (6 X 400 MM)
5609-400-M	3056945	PROBE, SECON. PRT, 100 OHM (6 X 400 MM)
5609-400-P	3376815	PROBE, SECON. PRT, 100 OHM (6 X 400 MM)
5609-400-S	3056950	PROBE, SECON. PRT, 100 OHM (6 X 400 MM)
5609-500-A	3561581	PROBE, SECON. PRT, 100 OHM (6 X 500 MM)
5609-500-B	3056961	PROBE, SECON. PRT, 100 OHM (6 X 500 MM)
5609-500-D	3056977	PROBE, SECON. PRT, 100 OHM (6 X 500 MM)
5609-500-G	3056989	PROBE, SECON. PRT, 100 OHM (6 X 500 MM)
5609-500-I	3056992	PROBE, SECON. PRT, 100 OHM (6 X 500 MM)
5609-500-J	3057004	PROBE, SECON. PRT, 100 OHM (6 X 500 MM)
5609-500-L	3057019	PROBE, SECON. PRT, 100 OHM (6 X 500 MM)
5609-500-M	3057028	PROBE, SECON. PRT, 100 OHM (6 X 500 MM)
5609-500-P	3376826	PROBE, SECON. PRT, 100 OHM (6 X 500 MM)
5609-500-S	3057037	PROBE, SECON. PRT, 100 OHM (6 X 500 MM)
5609-9BND-A	3116028	PROBE, SECON. PRT, 100 OHM,9IN 90 DEG BEND
5609-9BND-B	3116037	PROBE, SECON. PRT, 100 OHM,9IN 90 DEG BEND
5609-9BND-D	3116043	PROBE, SECON. PRT, 100 OHM,9IN 90 DEG BEND
5609-9BND-G	3116055	PROBE, SECON. PRT, 100 OHM,9IN 90 DEG BEND
5609-9BND-I	3116062	PROBE, SECON. PRT, 100 OHM,9IN 90 DEG BEND
5609-9BND-J	3116070	PROBE, SECON. PRT, 100 OHM,9IN 90 DEG BEND
5609-9BND-L	3116081	PROBE, SECON. PRT, 100 OHM,9IN 90 DEG BEND
5609-9BND-M	3116096	PROBE, SECON. PRT, 100 OHM,9IN 90 DEG BEND
5609-9BND-P	3376832	PROBE, SECON. PRT, 100 OHM,9IN 90 DEG BEND
5609-9BND-S	3116107	PROBE, SECON. PRT, 100 OHM,9IN 90 DEG BEND
5609-BEND-A	3116118	PROBE, SECON. PRT, 100 OHM, BEND
5609-BEND-B	3116129	PROBE, SECON. PRT, 100 OHM, BEND
5609-BEND-D	3116134	PROBE, SECON. PRT, 100 OHM, BEND
5609-BEND-G	3116141	PROBE, SECON. PRT, 100 OHM, BEND
5609-BEND-I	3116152	PROBE, SECON. PRT, 100 OHM, BEND
5609-BEND-J	3116165	PROBE, SECON. PRT, 100 OHM, BEND
5609-BEND-L	3116176	PROBE, SECON. PRT, 100 OHM, BEND
5609-BEND-M	3116183	PROBE, SECON. PRT, 100 OHM, BEND
5609-BEND-S	3116190	PROBE, SECON. PRT, 100 OHM, BEND
5610-6-B	1652473	PROBE, THERMISTOR 1/8IN X 6IN STAINLESS
5610-6-D	1652486	PROBE, THERMISTOR 1/8IN X 6IN STAINLESS
5610-6-G	1652506	PROBE, THERMISTOR 1/8IN X 6IN STAINLESS

Offer valid through December 31, 2016. Redemptions must be sent within 30 days of purchase.

Fluke Calibration Products Eligible for Accurate Power of Fluke Promotion

5610-6-I	1652514	PROBE, THERMISTOR 1/8IN X 6IN STAINLESS
5610-6-J	1652523	PROBE, THERMISTOR 1/8IN X 6IN STAINLESS
5610-6-L	1652538	PROBE, THERMISTOR 1/8IN X 6IN STAINLESS
5610-6-M	1652545	PROBE, THERMISTOR 1/8IN X 6IN STAINLESS
5610-6-P	3376859	PROBE, THERMISTOR 1/8X6 INCH SST
5610-6-S	1652550	PROBE, THERMISTOR 1/8IN X 6IN STAINLESS
5610-9-B	1652561	PROBE, THERMISTOR 1/8IN X 9IN STAINLESS
5610-9-D	1652577	PROBE, THERMISTOR 1/8IN X 9IN STAINLESS
5610-9-G	1652592	PROBE, THERMISTOR 1/8IN X 9IN STAINLESS
5610-9-I	1652605	PROBE, THERMISTOR 1/8IN X 9IN STAINLESS
5610-9-J	1652610	PROBE, THERMISTOR 1/8IN X 9IN STAINLESS
5610-9-L	1652622	PROBE, THERMISTOR 1/8IN X 9IN STAINLESS
5610-9-M	1652631	PROBE, THERMISTOR 1/8IN X 9IN STAINLESS
5610-9-P	3376867	PROBE, THERMISTOR 1/8X9 INCH SST
5610-9-S	1652646	PROBE, THERMISTOR 1/8IN X 9IN STAINLESS
5611A-11-B	2739928	PROBE, BARE THERMISTOR
5611A-11-D	2739937	PROBE, BARE THERMISTOR
5611A-11-G	2739955	PROBE, BARE THERMISTOR
5611A-11-I	2739943	PROBE, BARE THERMISTOR
5611A-11-J	2739962	PROBE, BARE THERMISTOR
5611A-11-L	2739919	PROBE, BARE THERMISTOR
5611A-11-M	2739970	PROBE, BARE THERMISTOR
5611A-11-O	3623464	PROBE, BARE THERMISTOR, INFO-CON (BIO-RAD)
5611A-11-P	3376871	PROBE, SILICONE BEAD THERMISTOR
5611A-11-S	2739981	PROBE, BARE THERMISTOR
5611T-B	2740014	PROBE, BARE THERMISTOR - TEFLON
5611T-D	2740023	PROBE, BARE THERMISTOR - TEFLON
5611T-G	2740045	PROBE, BARE THERMISTOR - TEFLON
5611T-I	2740038	PROBE, BARE THERMISTOR - TEFLON
5611T-J	2740050	PROBE, BARE THERMISTOR - TEFLON
5611T-L	2740006	PROBE, BARE THERMISTOR - TEFLON
5611T-M	2740061	PROBE, BARE THERMISTOR - TEFLON
5611T-P	3376880	PROBE, BARE THERMISTOR - TEFLON
5611T-S	2767216	PROBE, BARE THERMISTOR - TEFLON
5615-12-A	3055399	PROBE, SECON. PRT, 100 OHM (1/4 X 12 INCH)
5615-12-B	3002831	PROBE, SECON. PRT, 100 OHM (1/4 X 12 INCH)
5615-12-D	3002846	PROBE, SECON. PRT, 100 OHM (1/4 X 12 INCH)
5615-12-G	3002854	PROBE, SECON. PRT, 100 OHM (1/4 X 12 INCH)
5615-12-I	3002868	PROBE, SECON. PRT, 100 OHM (1/4 X 12 INCH)
5615-12-J	3002879	PROBE, SECON. PRT, 100 OHM (1/4 X 12 INCH)
5615-12-L	3002887	PROBE, SECON. PRT, 100 OHM (1/4 X 12 INCH)
5615-12-M	3002893	PROBE, SECON. PRT, 100 OHM (1/4 X 12 INCH)
5615-12-P	3376898	PROBE, SECON. PRT, 100 OHM (1/4 X 12 INCH)
5615-12-S	3002902	PROBE, SECON. PRT, 100 OHM (1/4 X 12 INCH)
5615-6-A	3055386	PROBE, SECON. PRT, 100 OHM (3/16 X 6 INCH)
5615-6-B	3002676	PROBE, SECON. PRT, 100 OHM (3/16 X 6 INCH)
5615-6-D	3002683	PROBE, SECON. PRT, 100 OHM (3/16 X 6 INCH)
5615-6-G	3002690	PROBE, SECON. PRT, 100 OHM (3/16 X 6 INCH)
5615-6-I	3002708	PROBE, SECON. PRT, 100 OHM (3/16 X 6 INCH)
5615-6-J	3002713	PROBE, SECON. PRT, 100 OHM (3/16 X 6 INCH)
5615-6-L	3002724	PROBE, SECON. PRT, 100 OHM (3/16 X 6 INCH)
5615-6-M	3002736	PROBE, SECON. PRT, 100 OHM (3/16 X 6 INCH)
5615-6-P	3376906	PROBE, SECON. PRT, 100 OHM (3/16 X 6 INCH)
5615-6-S	3002749	PROBE, SECON. PRT, 100 OHM (3/16 X 6 INCH)
5615-9-A	3055373	PROBE, SECON. PRT, 100 OHM (3/16 X 9 INCH)
5615-9-B	3002751	PROBE, SECON. PRT, 100 OHM (3/16 X 9 INCH)
5615-9BND-A	4682875	PROBE, SECON. PRT, 100 OHM,9IN 90 DEG BEND
5615-9BND-B	4682882	PROBE, SECON. PRT, 100 OHM,9IN 90 DEG BEND
5615-9BND-D	4682894	PROBE, SECON. PRT, 100 OHM,9IN 90 DEG BEND
5615-9BND-G	4682907	PROBE, SECON. PRT, 100 OHM,9IN 90 DEG BEND
5615-9BND-I	4682918	PROBE, SECON. PRT, 100 OHM,9IN 90 DEG BEND
5615-9BND-J	4682929	PROBE, SECON. PRT, 100 OHM,9IN 90 DEG BEND
5615-9BND-L	4682934	PROBE, SECON. PRT, 100 OHM,9IN 90 DEG BEND

Offer valid through December 31, 2016. Redemptions must be sent within 30 days of purchase.

Fluke Calibration Products Eligible for Accurate Power of Fluke Promotion

5615-9BND-M	4682941	PROBE, SECON. PRT, 100 OHM,9IN 90 DEG BEND
5615-9BND-P	4682952	PROBE, SECON. PRT, 100 OHM,9IN 90 DEG BEND
5615-9BND-S	4682965	PROBE, SECON. PRT, 100 OHM,9IN 90 DEG BEND
5615-9-D	3002760	PROBE, SECON. PRT, 100 OHM (3/16 X 9 INCH)
5615-9-G	3002772	PROBE, SECON. PRT, 100 OHM (3/16 X 9 INCH)
5615-9-I	3002785	PROBE, SECON. PRT, 100 OHM (3/16 X 9 INCH)
5615-9-J	3002797	PROBE, SECON. PRT, 100 OHM (3/16 X 9 INCH)
5615-9-L	3002805	PROBE, SECON. PRT, 100 OHM (3/16 X 9 INCH)
5615-9-M	3002810	PROBE, SECON. PRT, 100 OHM (3/16 X 9 INCH)
5615-9-P	3376914	PROBE, SECON. PRT, 100 OHM (3/16 X 9 INCH)
5615-9-S	3002822	PROBE, SECON. PRT, 100 OHM (3/16 X 9 INCH)
5615-BEND-A	3055402	PROBE, SECON. PRT, 100 OHM, 90 BEND
5615-BEND-D	3002925	PROBE, SECON. PRT, 100 OHM, 90 BEND
5616-12-A	3277531	PROBE, SECON. PRT, 100 OHM (1/4 X 12 INCH)
5616-12-B	3032648	PROBE, SECON. PRT, 100 OHM (1/4 X 12 INCH)
5616-12-D	3032653	PROBE, SECON. PRT, 100 OHM (1/4 X 12 INCH)
5616-12-G	3032666	PROBE, SECON. PRT, 100 OHM (1/4 X 12 INCH)
5616-12-I	3032675	PROBE, SECON. PRT, 100 OHM (1/4 X 12 INCH)
5616-12-J	3032682	PROBE, SECON. PRT, 100 OHM (1/4 X 12 INCH)
5616-12-L	3032694	PROBE, SECON. PRT, 100 OHM (1/4 X 12 INCH)
5616-12-M	3032701	PROBE, SECON. PRT, 100 OHM (1/4 X 12 INCH)
5616-12-P	3376961	PROBE, SECON. PRT, 100 OHM (1/4 X 12 INCH)
5616-12-S	3032712	PROBE, SECON. PRT, 100 OHM (1/4 X 12 INCH)
5618B-12-A	4623267	PROBE, SECON. PRT, 12 X 1/8 INCH OD
5618B-12-B	3003240	PROBE, SECON. PRT, 12 X 1/8 INCH OD
5618B-12-D	3003257	PROBE, SECON. PRT, 12 X 1/8 INCH OD
5618B-12-G	3003269	PROBE, SECON. PRT, 12 X 1/8 INCH OD
5618B-12-I	3003278	PROBE, SECON. PRT, 12 X 1/8 INCH OD
5618B-12-J	3003284	PROBE, SECON. PRT, 12 X 1/8 INCH OD
5618B-12-L	3003291	PROBE, SECON. PRT, 12 X 1/8 INCH OD
5618B-12-M	3003305	PROBE, SECON. PRT, 12 X 1/8 INCH OD
5618B-12-P	3376977	PROBE, SECON. PRT, 12 X 1/8 INCH OD
5618B-12-S	3003310	PROBE, SECON. PRT, 12 X 1/8 INCH OD
5618B-6-B	3003322	PROBE, SECON. PRT, 6 X 1/8 INCH OD
5618B-6-D	3003331	PROBE, SECON. PRT, 6 X 1/8 INCH OD
5618B-6-G	3003346	PROBE, SECON. PRT, 6 X 1/8 INCH OD
5618B-6-I	3003354	PROBE, SECON. PRT, 6 X 1/8 INCH OD
5618B-6-J	3003368	PROBE, SECON. PRT, 6 X 1/8 INCH OD
5618B-6-L	3003379	PROBE, SECON. PRT, 6 X 1/8 INCH OD
5618B-6-M	3003387	PROBE, SECON. PRT, 6 X 1/8 INCH OD
5618B-6-P	3376989	PROBE, SECON. PRT, 6 X 1/8 INCH OD
5618B-6-S	3003393	PROBE, SECON. PRT, 6 X 1/8 INCH OD
5618B-9-A	4222343	PROBE, SECON. PRT, 9 X 1/8 INCH OD
5618B-9-B	3003400	PROBE, SECON. PRT, 9 X 1/8 INCH OD
5618B-9-D	3003417	PROBE, SECON. PRT, 9 X 1/8 INCH OD
5618B-9-G	3003421	PROBE, SECON. PRT, 9 X 1/8 INCH OD
5618B-9-I	3003439	PROBE, SECON. PRT, 9 X 1/8 INCH OD
5618B-9-J	3003442	PROBE, SECON. PRT, 9 X 1/8 INCH OD
5618B-9-L	3003456	PROBE, SECON. PRT, 9 X 1/8 INCH OD
5618B-9-M	3003463	PROBE, SECON. PRT, 9 X 1/8 INCH OD
5618B-9-P	3376992	PROBE, SECON. PRT, 9 X 1/8 INCH OD
5618B-9-S	3003474	PROBE, SECON. PRT, 9 X 1/8 INCH OD
5622-05-B	1653385	PROBE, FAST RESPONSE PRT, 0.5MM DIA.
5622-05-D	1653397	PROBE, FAST RESPONSE PRT, 0.5MM DIA.
5622-05-G	1653415	PROBE, FAST RESPONSE PRT, 0.5MM DIA.
5622-05-I	1653426	PROBE, FAST RESPONSE PRT, 0.5MM DIA.
5622-05-J	1653432	PROBE, FAST RESPONSE PRT, 0.5MM DIA.
5622-05-L	1653444	PROBE, FAST RESPONSE PRT, 0.5MM DIA.
5622-05-M	1653459	PROBE, FAST RESPONSE PRT, 0.5MM DIA.
5622-05-P	3377004	PRT, FAST RESPONSE, 0.5 MM DIA, 100 OHM
5622-05-S	1653467	PROBE, FAST RESPONSE PRT, 0.5MM DIA.
5622-10-B	1653471	PROBE, FAST RESPONSE PRT, 1.0 MM DIA.
5622-10-D	1653480	PROBE, FAST RESPONSE PRT, 1.0 MM DIA.

Offer valid through December 31, 2016. Redemptions must be sent within 30 days of purchase.

Fluke Calibration Products Eligible for Accurate Power of Fluke Promotion

5622-10-G	1653500	PROBE, FAST RESPONSE PRT, 1.0 MM DIA.
5622-10-I	1653517	PROBE, FAST RESPONSE PRT, 1.0 MM DIA.
5622-10-J	1653521	PROBE, FAST RESPONSE PRT, 1.0 MM DIA.
5622-10-L	1653539	PROBE, FAST RESPONSE PRT, 1.0 MM DIA.
5622-10-M	1653542	PROBE, FAST RESPONSE PRT, 1.0 MM DIA.
5622-10-P	3377019	PRT, FAST RESPONSE, 1.0 MM DIA, 100 OHM
5622-10-S	1653556	PROBE, FAST RESPONSE PRT, 1.0 MM DIA.
5622-16-B	1653563	PROBE, FAST RESPONSE PRT, 1.6 MM DIA.
5622-16-D	1653574	PROBE, FAST RESPONSE PRT, 1.6 MM DIA.
5622-16-G	1653595	PROBE, FAST RESPONSE PRT, 1.6 MM DIA.
5622-16-I	1653602	PROBE, FAST RESPONSE PRT, 1.6 MM DIA.
5622-16-J	1653616	PROBE, FAST RESPONSE PRT, 1.6 MM DIA.
5622-16-L	1653625	PROBE, FAST RESPONSE PRT, 1.6 MM DIA.
5622-16-M	1653633	PROBE, FAST RESPONSE PRT, 1.6 MM DIA.
5622-16-P	3377028	PRT, FAST RESPONSE, 1.6 MM DIA, 100 OHM
5622-16-S	1653640	PROBE, FAST RESPONSE PRT, 1.6 MM DIA.
5622-32-B	1653657	PROBE, FAST RESPONSE PRT, 3.2MM DIA.
5622-32-D	1653669	PROBE, FAST RESPONSE PRT, 3.2MM DIA.
5622-32-G	1653684	PROBE, FAST RESPONSE PRT, 3.2MM DIA.
5622-32-I	1653691	PROBE, FAST RESPONSE PRT, 3.2MM DIA.
5622-32-J	1653706	PROBE, FAST RESPONSE PRT, 3.2MM DIA.
5622-32-L	1653714	PROBE, FAST RESPONSE PRT, 3.2MM DIA.
5622-32-M	1653723	PROBE, FAST RESPONSE PRT, 3.2MM DIA.
5622-32-P	3377037	PRT, FAST RESPONSE, 3.2 MM DIA, 100 OHM
5622-32-S	1653738	PROBE, FAST RESPONSE PRT, 3.2MM DIA.
5623B-6-B	3003488	PROBE, INDUSTRIAL PRT, 1/4 X 6 INCH, FREEZER
5623B-6-D	3003495	PROBE, INDUSTRIAL PRT, 1/4 X 6 INCH, FREEZER
5623B-6-G	3003508	PROBE, INDUSTRIAL PRT, 1/4 X 6 INCH, FREEZER
5623B-6-I	3003513	PROBE, INDUSTRIAL PRT, 1/4 X 6 INCH, FREEZER
5623B-6-J	3003524	PROBE, INDUSTRIAL PRT, 1/4 X 6 INCH, FREEZER
5623B-6-L	3003536	PROBE, INDUSTRIAL PRT, 1/4 X 6 INCH, FREEZER
5623B-6-M	3003549	PROBE, INDUSTRIAL PRT, 1/4 X 6 INCH, FREEZER
5623B-6-P	3377043	PROBE, INDUSTRIAL PRT, 1/4 X 6 INCH, FREEZER
5623B-6-S	3003551	PROBE, INDUSTRIAL PRT, 1/4 X 6 INCH, FREEZER
5626-12-A	3055440	PROBE, SEC. PRT, 100 OHM 1/4 DIA X 12 (IN)
5626-12-B	1653830	PROBE, SEC. PRT, 100 OHM 1/4IN DIA X 12IN
5626-12-D	1653848	PROBE, SEC. PRT, 100 OHM 1/4IN DIA X 12IN
5626-12-G	1653866	PROBE, SEC. PRT, 100 OHM 1/4IN DIA X 12IN
5626-12-I	1653875	PROBE, SEC. PRT, 100 OHM 1/4IN DIA X 12IN
5626-12-J	1653882	PROBE, SEC. PRT, 100 OHM 1/4IN DIA X 12IN
5626-12-L	1653894	PROBE, SEC. PRT, 100 OHM 1/4IN DIA X 12IN
5626-12-M	1653907	PROBE, SEC. PRT, 100 OHM 1/4IN DIA X 12IN
5626-12-P	3377055	PROBE, SEC. PRT, 100 OHM 1/4 IN DIA X 12 INCH
5626-12-S	1653918	PROBE, SEC. PRT, 100 OHM 1/4IN DIA X 12IN
5626-15-A	3055457	PROBE, SEC. PRT, 100 OHM 1/4 DIA X 15 (IN)
5626-15-B	1653929	PROBE, SEC. PRT, 100 OHM 1/4IN DIA X 15IN
5626-15-D	1653934	PROBE, SEC. PRT, 100 OHM 1/4IN DIA X 15IN
5626-15-G	1653952	PROBE, SEC. PRT, 100 OHM 1/4IN DIA X 15IN
5626-15-I	1653965	PROBE, SEC. PRT, 100 OHM 1/4IN DIA X 15IN
5626-15-J	1653976	PROBE, SEC. PRT, 100 OHM 1/4IN DIA X 15IN
5626-15-L	1653983	PROBE, SEC. PRT, 100 OHM 1/4IN DIA X 15IN
5626-15-M	1653990	PROBE, SEC. PRT, 100 OHM 1/4IN DIA X 15IN
5626-15-P	3377062	PROBE, SEC. PRT, 100 OHM 1/4 IN DIA X 15 INCH
5626-15-S	1654000	PROBE, SEC. PRT, 100 OHM 1/4IN DIA X 15IN
5626-20-A	3055469	PROBE, SEC. PRT, 100 OHM 1/4 DIA X 20 (IN)
5626-20-B	2451974	PROBE, SEC. PRT, 100 OHM, 1/4 IN X 20 IN
5626-20-D	2451988	PROBE, SEC. PRT, 100 OHM, 1/4 IN X 20 IN
5626-20-G	2452003	PROBE, SEC. PRT, 100 OHM, 1/4 IN X 20 IN
5626-20-I	2452015	PROBE, SEC. PRT, 100 OHM, 1/4 IN X 20 IN
5626-20-J	2452026	PROBE, SEC. PRT, 100 OHM, 1/4 IN X 20 IN
5626-20-L	2452032	PROBE, SEC. PRT, 100 OHM, 1/4 IN X 20 IN
5626-20-M	2452044	PROBE, SEC. PRT, 100 OHM, 1/4 IN X 20 IN
5626-20-P	3377070	PROBE, SEC. PRT, 100 OHM, 1/4X20 INCH

Offer valid through December 31, 2016. Redemptions must be sent within 30 days of purchase.

Fluke Calibration Products Eligible for Accurate Power of Fluke Promotion

5626-20-S	2452059	PROBE, SEC. PRT, 100 OHM, 1/4 IN X 20 IN
5627A-12-A	3055537	PROBE, RTD INDUSTRIAL 12 X 1/4 INCH OD
5627A-12-B	3003560	PROBE, RTD INDUSTRIAL 12 X 1/4 INCH OD
5627A-12-D	3003572	PROBE, RTD INDUSTRIAL 12 X 1/4 INCH OD
5627A-12-G	3003585	PROBE, RTD INDUSTRIAL 12 X 1/4 INCH OD
5627A-12-I	3003597	PROBE, RTD INDUSTRIAL 12 X 1/4 INCH OD
5627A-12-J	3003609	PROBE, RTD INDUSTRIAL 12 X 1/4 INCH OD
5627A-12-L	3003611	PROBE, RTD INDUSTRIAL 12 X 1/4 INCH OD
5627A-12-M	3003627	PROBE, RTD INDUSTRIAL 12 X 1/4 INCH OD
5627A-12-P	3377081	PROBE, RTD INDUSTRIAL 12 X 1/4 INCH OD
5627A-12-S	3003630	PROBE, RTD INDUSTRIAL 12 X 1/4 INCH OD
5627A-6-A	3055519	PROBE, RTD INDUSTRIAL 6 X 3/16 INCH OD
5627A-6-B	3003648	PROBE, RTD INDUSTRIAL 6 X 3/16 INCH OD
5627A-6-D	3003653	PROBE, RTD INDUSTRIAL 6 X 3/16 INCH OD
5627A-6-G	3003666	PROBE, RTD INDUSTRIAL 6 X 3/16 INCH OD
5627A-6-I	3003675	PROBE, RTD INDUSTRIAL 6 X 3/16 INCH OD
5627A-6-J	3003682	PROBE, RTD INDUSTRIAL 6 X 3/16 INCH OD
5627A-6-L	3003694	PROBE, RTD INDUSTRIAL 6 X 3/16 INCH OD
5627A-6-M	3003701	PROBE, RTD INDUSTRIAL 6 X 3/16 INCH OD
5627A-6-P	3377096	PROBE, RTD INDUSTRIAL 6 X 3/16 INCH OD
5627A-6-S	3003712	PROBE, RTD INDUSTRIAL 6 X 3/16 INCH OD
5627A-9-A	3055528	PROBE, RTD INDUSTRIAL 9 X 3/16 INCH OD
5627A-9-B	3003720	PROBE, RTD INDUSTRIAL 9 X 3/16 INCH OD
5627A-9-D	3003735	PROBE, RTD INDUSTRIAL 9 X 3/16 INCH OD
5627A-9-G	3003747	PROBE, RTD INDUSTRIAL 9 X 3/16 INCH OD
5627A-9-I	3003758	PROBE, RTD INDUSTRIAL 9 X 3/16 INCH OD
5627A-9-J	3003764	PROBE, RTD INDUSTRIAL 9 X 3/16 INCH OD
5627A-9-L	3003773	PROBE, RTD INDUSTRIAL 9 X 3/16 INCH OD
5627A-9-M	3003786	PROBE, RTD INDUSTRIAL 9 X 3/16 INCH OD
5627A-9-P	3377107	PROBE, RTD INDUSTRIAL 9 X 3/16 INCH OD
5627A-9-S	3003799	PROBE, RTD INDUSTRIAL 9 X 3/16 INCH OD
5627A-BEND-A	3055478	PROBE, RTD INDUSTRIAL 12 X 1/4 INCH, 90 BEND
5627A-BEND-B	3003806	PROBE, RTD INDUSTRIAL 12 X 1/4 INCH, 90 BEND
5627A-BEND-D	3003814	PROBE, RTD INDUSTRIAL 12 X 1/4 INCH, 90 BEND
5627A-BEND-L	3003850	PROBE, RTD INDUSTRIAL 12 X 1/4 INCH, 90 BEND
5627A-BEND-S	3003877	PROBE, RTD INDUSTRIAL 12 X 1/4 INCH, 90 BEND
6102-156	1656950	MICRO-BATH, 35 TO 200C, 110V 50/60HZ
7102-156	1657597	MICRO-BATH, -5 TO 125C, 110V 50/60HZ
7103-156	1657611	MICRO-BATH, -30 TO 125C, 110V 50/60HZ
7103-TR-156	2645215	MICRO-BATH, -20 TO 150C
7526A-156	4232116	PRECISION PROCESS CALIBRATOR, 115V
7526A-CASE	4232133	CASE, 7526A, CARRYING
9009-B-156	1657764	DRY-WELL, DUAL-BLOCK (BLACK), 110V 50/60HZ
9009-Y-156	1657786	DRY-WELL, DUAL-BLOCK (YELLOW), 110V 50/60HZ
9100S/725-KIT	4550143	HI-TEMP DRY-WELL & PROCESS CALIBRATOR BUNDLE
9100S-A-156	1885080	DRY-WELL, HANDHELD HI-TEMP, BLOCK A
9100S-B-156	1885116	DRY-WELL, HANDHELD HI-TEMP, BLOCK B
9100S-C-156	1885133	DRY-WELL, HANDHELD HI-TEMP, BLOCK C
9100S-D-156	1885157	DRY-WELL, HANDHELD HI-TEMP, BLOCK D (EURO)
9102S/725-KIT	4550155	TEMP DRY-WELL & PROCESS CALIBRATOR BUNDLE
9102S-156	1885178	DRY-WELL, HH LOW-TEMP
9103-A-156	1657926	DRY-WELL, FIELD W/ 3103-2, 110V 50/60HZ
9103-B-156	1657944	DRY-WELL, FIELD W/ 3103-3, 110V 50/60HZ
9103-C-156	1657967	DRY-WELL, FIELD W/ 3103-4, 110V 50/60HZ
9103-D-156	2001126	DRY-WELL, -25C FIELD W/ 3103-6, 115V
9103-DW-156	3015831	DRY-WELL, -25C FIELD, NO INSERT, 115V
9132-156	1658205	CALIBRATOR, IR, 110V 50/60HZ
9133-156	1658222	CALIBRATOR, IR, 110V 50/60HZ
9140-A-156	1658268	DRY-WELL, FIELD W/3140-2, 110V 50/60HZ
9140-B-156	1658287	DRY-WELL, FIELD W/3140-3, 110V 50/60HZ
9140-C-156	1658302	DRY-WELL, FIELD W/3140-4, 110V 50/60HZ
9140-D-156	2001167	DRY-WELL, MID-RANGE FIELD W/3140-6, 115V
9140-DW-156	3015854	DRY-WELL, MID-RANGE FIELD, NO INSERT, 115V

Offer valid through December 31, 2016. Redemptions must be sent within 30 days of purchase.

Fluke Calibration Products Eligible for Accurate Power of Fluke Promotion

9142-A-156	3054127	DRY-WELL, LOW-TEMP FIELD, W/9142-INSA, 115V
9142-A-P-156	3054148	DRY-WELL, FIELD, W/9142-INSA, W/BLT-IN ELCT 115V
9142-B-156	3054166	DRY-WELL, LOW-TEMP FIELD, W/9142-INSB, 115V
9142-B-P-156	3054182	DRY-WELL, FIELD, W/9142-INSB, W/BLT-IN ELCT 115V
9142-C-156	3054203	DRY-WELL, LOW-TEMP FIELD, W/9142-INSC, 115V
9142-CASE	3054520	CASE, 9142-4 CARRYING
9142-C-P-156	3054226	DRY-WELL, FIELD, W/9142-INSC, W/BLT-IN ELCT 115V
9142-D-156	3054244	DRY-WELL, LOW-TEMP FIELD, W/9142-INSD, 115V
9142-D-P-156	3054267	DRY-WELL, FIELD, W/9142-INSD, W/BLT-IN ELCT 115V
9142-DW-156	3054306	DRY-WELL, LOW-TEMP FIELD, NO INSERT, 115V
9142-DW-P-156	3054323	DRY-WELL, FIELD, NO INSERT, W/BLT-IN ELCT, 115V
9142-E-156	3054345	DRY-WELL, LOW-TEMP FIELD, W/9142-INSE, 115V
9142-E-P-156	3054361	DRY-WELL, FIELD, W/9142-INSE, W/BLT-IN ELCT 115V
9142-F-156	3054389	DRY-WELL, LOW-TEMP FIELD, W/9142-INSF, 115V
9142-F-P-156	3054404	DRY-WELL, FIELD, W/9142-INSF, W/BLT-IN ELCT 115V
9142-INSA	3054428	INSERT, A, 9142, MISC (IN) HLS
9142-INSB	3054437	INSERT, B, 9142, CMP (IN) HLS
9142-INSC	3054443	INSERT, C, 9142, 0.25 (IN) HLS
9142-INSD	3054455	INSERT, D, 9142, MISC (MM) HLS
9142-INSE	3054462	INSERT, E, 9142, 0.25 (IN) REF, MISC (MM) HLS
9142-INSF	3054470	INSERT, F, 9142, 0.25 (IN) REF, CMP (MM) HLS
9142-INSG	3054481	INSERT, G, 9142, EA TEST
9142-INST	3054512	INSERT, TEST, 9142
9142-INSZ	3054496	INSERT, BLANK, 9142
9143-A-156	3054547	DRY-WELL, MID-TEMP FIELD, W/9143-INSA, 115V
9143-A-P-156	3054564	DRY-WELL, FIELD, W/9143-INSA, W/BLT-IN ELCT 115V
9143-B-156	3054586	DRY-WELL, MID-TEMP FIELD, W/9143-INSB, 115V
9143-B-P-156	3054607	DRY-WELL, FIELD, W/9143-INSB, W/BLT-IN ELCT 115V
9143-C-156	3054629	DRY-WELL, MID-TEMP FIELD, W/9143-INSC, 115V
9143-C-P-156	3054641	DRY-WELL, FIELD, W/9143-INSC, W/BLT-IN ELCT 115V
9143-D-156	3054665	DRY-WELL, MID-TEMP FIELD, W/9143-INSD, 115V
9143-D-P-156	3054683	DRY-WELL, FIELD, W/9143-INSD, W/BLT-IN ELCT 115V
9143-DW-156	3054724	DRY-WELL, MID-TEMP FIELD, NO INSERT, 115V
9143-DW-P-156	3054749	DRY-WELL, FIELD, NO INSERT, W/BLT-IN ELCT 115V
9143-E-156	3054760	DRY-WELL, MID-TEMP FIELD, W/9143-INSE, 115V
9143-E-P-156	3054785	DRY-WELL, FIELD, W/9143-INSE, W/BLT-IN ELCT 115V
9143-F-156	3054805	DRY-WELL, MID-TEMP FIELD, W/9143-INSF, 115V
9143-F-P-156	3054822	DRY-WELL, FIELD, W/9143-INSF, W/BLT-IN ELCT 115V
9143-INSA	3054846	INSERT, A, 9143, MISC (IN) HLS
9143-INSB	3054854	INSERT, B, 9143, CMP (IN) HLS
9143-INSC	3054868	INSERT, C, 9143, 0.25 (IN) HLS
9143-INSD	3054879	INSERT, D, 9143, MISC (MM) HLS
9143-INSE	3054887	INSERT, E, 9143, 0.25 (IN) REF, MISC (MM) HLS
9143-INSF	3054893	INSERT, F, 9143, 0.25 (IN) REF, CMP (MM) HLS
9143-INSG	3054902	INSERT, G, 9143, EA TEST
9143-INST	3054933	INSERT, TEST, 9143
9143-INSZ	3054916	INSERT, BLANK, 9143
9144-A-156	3054940	DRY-WELL, HIGH-TEMP FIELD, W/9144-INSA, 115V
9144-A-P-156	3054969	DRY-WELL, FIELD, W/9144-INSA, W/BLT-IN ELCT 115V
9144-B-156	3054984	DRY-WELL, HIGH-TEMP FIELD, W/9144-INSB, 115V
9144-B-P-156	3055008	DRY-WELL, FIELD, W/9144-INSB, W/BLT-IN ELCT 115V
9144-C-156	3055024	DRY-WELL, HIGH-TEMP FIELD, W/9144-INSC, 115V
9144-C-P-156	3055049	DRY-WELL, FIELD, W/9144-INSC, W/BLT-IN ELCT 115V
9144-D-156	3055060	DRY-WELL, HIGH-TEMP FIELD, W/9144-INSD, 115V
9144-D-P-156	3055085	DRY-WELL, FIELD, W/9144-INSD, W/BLT-IN ELCT 115V
9144-DW-156	3055123	DRY-WELL, HIGH-TEMP FIELD, NO INSERT, 115V
9144-DW-P-156	3055145	DRY-WELL, FIELD, NO INSERT, W/BLT-IN ELCT 115V
9144-E-156	3055161	DRY-WELL, HIGH-TEMP FIELD, W/9144-INSE, 115V
9144-E-P-156	3055189	DRY-WELL, FIELD, W/9144-INSE, W/BLT-IN ELCT 115V
9144-F-156	3055200	DRY-WELL, HIGH-TEMP FIELD, W/9144-INSF, 115V
9144-F-P-156	3055221	DRY-WELL, FIELD, W/9144-INSF, W/BLT-IN ELCT 115V
9144-INSA	3055242	INSERT, A, 9144, MISC HLS
9144-INSB	3055256	INSERT, B, 9144, CMP HLS

Offer valid through December 31, 2016. Redemptions must be sent within 30 days of purchase.

Fluke Calibration Products Eligible for Accurate Power of Fluke Promotion

9144-INSC	3055263	INSERT, C,9144, FOUR 0.25 IN HLS
9144-INS D	3055274	INSERT, D,9144, METRIC, MISC HLS
9144-INSE	3055288	INSERT, E,9144, METRIC,0.25 IN REF,MISC HLS
9144-INSF	3055295	INSERT, F,9144, METRIC,0.25 IN REF,CMP HLS
9144-INSG	3055301	INSERT, G, 9144, EA TEST
9144-INST	3055335	INSERT, TEST, 9144
9144-INSZ	3055312	INSERT, BLANK, 9144
9150-A-156	1658384	FURNACE, 1200C TC W/3150-2, 110V 50/60HZ
9150-B-156	1658406	FURNACE, 1200C TC W/3150-3, 110V 50/60HZ
9150-C-156	1658423	FURNACE, 1200C TC W/3150-4, 110V 50/60HZ
9150-D-156	2001209	FURNACE, 12000C TC W/3150-5, 115V
9150-DW-156	3015902	FURNACE, 1200C TC, NO INSERT, 115V
9170-A-156	2458800	METROLOGY WELL, -45C, W/9170-INSA, 115V
9170-A-R-156	2458821	METROLOGY WELL, -45C,W/9170-INSA,W/REF, 115V
9170-B-156	2458842	METROLOGY WELL, -45C, W/9170-INSB, 115V
9170-B-R-156	2458863	METROLOGY WELL, -45C,W/9170-INSB,W/REF, 115V
9170-C-156	2458888	METROLOGY WELL, -45C, W/9170-INSC, 115V
9170-CASE	2460086	CASE, 9170-3 CARRYING
9170-C-R-156	2458901	METROLOGY WELL, -45C,W/9170-INSC,W/REF, 115V
9170-D-156	2458920	METROLOGY WELL, -45C, W/9170-INS D, 115V
9170-DCAS	2460099	CASE, DISTRIBUTOR, 9170-3 CARRYING
9170-D-R-156	2458947	METROLOGY WELL, -45C,W/9170-INS D,W/REF, 115V
9170-DW-156	3015925	METROLOGY WELL, -45C, NO INSERT, 115V
9170-DW-R-156	3015940	METROLOGY WELL,-45C,NO INSRT,W/BLTIN REF,115V
9170-E-156	2458964	METROLOGY WELL, -45C, W/9170-INSE, 115V
9170-E-R-156	2458986	METROLOGY WELL, -45C,W/9170-INSE,W/REF, 115V
9170-F-156	2459006	METROLOGY WELL, -45C, W/9170-INSF, 115V
9170-F-R-156	2459023	METROLOGY WELL, -45C,W/9170-INSF,W/REF, 115V
9170-INSA	2459766	INSERT, A, 9170, MISC HLS
9170-INSB	2459775	INSERT, B, 9170, CMP HLS
9170-INSC	2459782	INSERT, C,9170, FOUR 0.25 IN HLS
9170-INS D	2459794	INSERT, D,9170, METRIC, MISC HLS
9170-INSE	2459802	INSERT, E,9170, METRIC,0.25 IN REF,MISC HLS
9170-INSF	2459816	INSERT, F,9170, METRIC,0.25 IN REF,CMP HLS
9170-INSZ	2459833	INSERT, BLANK, 9170
9171-A-156	2459045	METROLOGY WELL, -30C, W/9171-INSA, 115V
9171-A-R-156	2459061	METROLOGY WELL, -30C,W/9171-INSA,W/REF, 115V
9171-B-156	2459089	METROLOGY WELL, -30C, W/9171-INSB, 115V
9171-B-R-156	2459108	METROLOGY WELL, -30C,W/9171-INSB,W/REF, 115V
9171-C-156	2459124	METROLOGY WELL, -30C, W/9171-INSC, 115V
9171-C-R-156	2459149	METROLOGY WELL, -30C,W/9171-INSC,W/REF, 115V
9171-D-156	2459160	METROLOGY WELL, -30C, W/9171-INS D, 115V
9171-D-R-156	2459185	METROLOGY WELL, -30C,W/9171-INS D,W/REF, 115V
9171-DW-156	3015969	METROLOGY WELL, -30C, NO INSERT, 115V
9171-DW-R-156	3015984	METROLOGY WELL,-30C,NO INSRT,W/BLTIN REF,115V
9171-E-156	2459201	METROLOGY WELL, -30C, W/9171-INSE, 115V
9171-E-R-156	2459220	METROLOGY WELL, -30C,W/9171-INSE,W/REF, 115V
9171-F-156	2459247	METROLOGY WELL, -30C, W/9171-INSF, 115V
9171-F-R-156	2459264	METROLOGY WELL, -30C,W/9171-INSF,W/REF, 115V
9171-INSA	2459840	INSERT, A,9171, MISC HLS
9171-INSB	2459857	INSERT, B,9171, CMP HLS
9171-INSC	2459869	INSERT, C,9171, SIX 0.25 IN HLS
9171-INS D	2459878	INSERT, D,9171, METRIC MISC HLS
9171-INSE	2459884	INSERT, E,9171, METRIC,0.25 IN REF,MISC HLS
9171-INSF	2459891	INSERT, F,9171, METRIC,0.25 IN REF,CMP HLS
9171-INSZ	2459910	INSERT, BLANK, 9171
9172-A-156	2459286	METROLOGY WELL, 425C, W/9172-INSA, 115V
9172-A-R-156	2459300	METROLOGY WELL, 425C,W/9172-INSA,W/REF, 115V
9172-B-156	2459321	METROLOGY WELL, 425C, W/9172-INSB, 115V
9172-B-R-156	2459342	METROLOGY WELL, 425C,W/9172-INSB,W/REF, 115V
9172-C-156	2459363	METROLOGY WELL, 425C, W/9172-INSC, 115V
9172-C-R-156	2459388	METROLOGY WELL, 425C,W/9172-INSC,W/REF, 115V
9172-D-156	2459407	METROLOGY WELL, 425C, W/9172-INS D, 115V

Offer valid through December 31, 2016. Redemptions must be sent within 30 days of purchase.

Fluke Calibration Products Eligible for Accurate Power of Fluke Promotion

9172-D-R-156	2459429	METROLOGY WELL, 425C,W/9172-INSR,W/REF, 115V
9172-DW-156	3016008	METROLOGY WELL, 425C, NO INSERT, 115V
9172-DW-R-156	3016024	METROLOGY WELL,425C,NO INSR,W/BLTIN REF,115V
9172-E-156	2459441	METROLOGY WELL, 425C, W/9172-INSE, 115V
9172-E-R-156	2459465	METROLOGY WELL, 425C,W/9172-INSE,W/REF, 115V
9172-F-156	2459483	METROLOGY WELL, 425C, W/9172-INSF, 115V
9172-F-R-156	2459503	METROLOGY WELL, 425C,W/9172-INSF,W/REF, 115V
9172-INSA	2459922	INSERT, A,9172, MISC HLS
9172-INSB	2459931	INSERT, B,9172, CMP HLS
9172-INSC	2459946	INSERT, C,9172, SIX 0.25 IN HLS
9172-INSD	2459954	INSERT, D,9172, METRIC MISC HLS
9172-INSE	2459968	INSERT, E,9172, METRIC,0.25 IN REF,MISC HLS
9172-INSF	2459979	INSERT, F,9172, METRIC,0.25 IN REF,CMP HLS
9172-INSZ	2459993	INSERT, BLANK, 9172
9173-A-156	2459526	METROLOGY WELL, 700C, W/9173-INSA, 115V
9173-A-R-156	2459544	METROLOGY WELL, 700C,W/9173-INSA,W/REF, 115V
9173-B-156	2459567	METROLOGY WELL, 700C, W/9173-INSB, 115V
9173-B-R-156	2459580	METROLOGY WELL, 700C,W/9173-INSB,W/REF, 115V
9173-C-156	2459604	METROLOGY WELL, 700C, W/9173-INSC, 115V
9173-C-R-156	2459628	METROLOGY WELL, 700C,W/9173-INSC,W/REF, 115V
9173-D-156	2459643	METROLOGY WELL, 700C, W/9173-INSR, 115V
9173-D-R-156	2459662	METROLOGY WELL, 700C,W/9173-INSR,W/REF, 115V
9173-DW-156	3016049	METROLOGY WELL, 700C, NO INSERT, 115V
9173-DW-R-156	3016060	METROLOGY WELL,700C,NO INSR,W/BLTIN REF,115V
9173-E-156	2459681	METROLOGY WELL, 700C, W/9173-INSE, 115V
9173-E-R-156	2459709	METROLOGY WELL, 700C,W/9173-INSE,W/REF, 115V
9173-F-156	2459727	METROLOGY WELL, 700C, W/9173-INSF, 115V
9173-F-R-156	2459748	METROLOGY WELL, 700C,W/9173-INSF,W/REF, 115V
9173-INSA	2460001	INSERT, A,9173, MISC HLS
9173-INSB	2460012	INSERT, B,9173, CMP HLS
9173-INSC	2460020	INSERT, C,9173, FOUR 0.25 IN HLS
9173-INSR	2460035	INSERT, D,9173, METRIC MISC HLS
9173-INSE	2460047	INSERT, E,9173, METRIC,0.25 IN REF,MISC HLS
9173-INSF	2460058	INSERT, F, 9173, METRIC,0.25 IN REF,CMP HLS
9173-INSZ	2460073	INSERT, BLANK, 9173
9190A-A-156	4178780	DRY-WELL, ULTRA-COLD, INSR-A, 115V
9190A-A-DKIT-156	4319570	DRY-WELL, ULTRA-COLD, INSR-A, 115V, DIST
9190A-A-P-156	4178800	DRY-WELL,ULTRA-COLD,INSR-A,BLT-IN ELCT, 115V
9190A-B-156	4178821	DRY-WELL, ULTRA-COLD, INSR-B, 115V
9190A-B-P-156	4178842	DRY-WELL,ULTRA-COLD,INSR-B,BLT-IN ELCT, 115V
9190A-C-156	4178863	DRY-WELL, ULTRA-COLD, INSR-C, 115V
9190A-C-P-156	4178888	DRY-WELL,ULTRA-COLD,INSR-C,BLT-IN ELCT, 115V
9190A-D-156	4178901	DRY-WELL, ULTRA-COLD, INSR-D, 115V
9190A-D-P-156	4178920	DRY-WELL,ULTRA-COLD,INSR-D,BLT-IN ELCT, 115V
9190A-DW-156	4178947	DRY-WELL, ULTRA-COLD, NO INSR, 115V
9190A-DW-P-156	4178964	DRY-WELL,ULTRA-COLD,NO INSR,BLT-IN ELCT,115V
9190A-E-156	4178986	DRY-WELL, ULTRA-COLD, INSR-E, 115V
9190A-E-P-156	4179006	DRY-WELL,ULTRA-COLD,INSR-E,BLT-IN ELCT, 115V
9190A-F-156	4179023	DRY-WELL, ULTRA-COLD, INSR-F, 115V
9190A-F-P-156	4179045	DRY-WELL,ULTRA-COLD,INSR-F,BLT-IN ELCT, 115V
9190-CASE	4231689	CASE, 9190, CARRYING
9190-INSA	4231692	INSERT, A, 9190, MISC HLS
9190-INSB	4231704	INSERT, B, 9190, CMP HLS
9190-INSC	4231719	INSERT, C, 9190, FOUR .25 IN HLS
9190-INSR	4231728	INSERT, D, 9190, METRIC, MISC HLS
9190-INSE	4231737	INSERT, E, 9190, METRIC, 0.25 IN REF, MISC HLS
9190-INSF	4231743	INSERT, F, 9190, METRIC, 0.25 IN REF, CMP HLS
9190-INSG	4231755	INSERT, G, 9190, EA TEST
9190-INST	4231762	INSERT, T, 9190, CALIBRATION TEST
9190-INSY1	4231770	INSERT, CUSTOM, 9190, WITH BLANK INSULATOR
9190-INSY2	4319562	INSERT, CUSTOM, 9190, WITH CUSTOM INSULATOR
9190-INSZ	4231781	INSERT, BLANK, 9190
Y1586D	4410483	RACK MOUNT KIT, DUAL (FULL RACK)

Offer valid through December 31, 2016. Redemptions must be sent within 30 days of purchase.

Fluke Calibration Products Eligible for Accurate Power of Fluke Promotion

Y1586S	4410476	RACK MOUNT KIT, SINGLE (HALF RACK)
Y7526A	4233827	RACK MOUNT KIT

FUSE MODEL NUMBER & RATING							
DMM MODELS	0.44A/ 1000V	630ma/ 250V	1A/ 600V	11A/ 1000V	15A/ 600V	2A/ 250V	3A/ 600V
73-2, 78					F2/F1		
21-2, 23-2, 75-2, 77-2		F1			F2		
29-2, 76			F1		F2		
21-3, 73-3, 75-3		F1		F2			
23-3, 26-3, 77-3, 79-3	F1			F2			
83, 85, 87 S/N <65650001 No CAT rating, 88			F1		F2		
83, 85, 87 S/N >65650001 CAT III rating	F1			F2			
83-3, 85-3, 87-3, 87E-3, 83-5,87-5,87-5/E, 88-5	F1			F2			
863, 865, 867, 867B	F2			F1			
25, 27		F2			F3		F1
27 >7247001 CAT III rating	F1			F3			
8060A, 8062A						F1	F2
111, 112				F1			
175, 177, 179, 187, 189	F1			F2			

FUSE CIRCUIT SYMBOLS

Note: F1/F2/F3 are fuse circuit symbols found in the Operator's Manual under "list of Operator Replacement Parts"