

TECHNICAL DATA

Ti480, Ti450, Ti400 and Ti300 Thermal Imagers

The Fluke Professional Series



SUPERIOR IMAGE QUALITY

SPATIAL RESOLUTION

Ti480 0.93 mRad

Ti450 and Ti400 1.31 mRad

Ti300 1.75 mRad

RESOLUTION

Ti480 640 x 480

SuperResolution mode: 1280 x 960

Ti450 320 x 240

SuperResolution mode: 640 x 480

Ti400 320 x 240

Ti300 240 x 180

FIELD OF VIEW

Ti480 34 °H x 24 °V

Ti450, Ti400, Ti300 24 °H x 17 °V




Fluke Connect® compatible

Focus redefined.

- Capture a clear, accurate image focused throughout the field of view with MultiSharp™ Focus. Simply point and shoot—the camera automatically processes a stack of images focused near and far (Ti480 and Ti450)
- Get an instant in-focus image of your designated target.
 LaserSharp* Auto Focus, exclusive to Fluke, uses a built-in laser distance meter that calculates and displays the distance from your designated target with pinpoint* accuracy
- Get 4x the pixel data with **SuperResolution**, which captures multiple images and combines them to create a 1280 x 960 image (Ti480) or a 640 x 480 image (Ti450)
- Save time—wirelessly sync images directly from your camera to the **Fluke Connect® system**, and attach to an asset record or work order. Make faster decisions by accessing inspection measurements from anywhere. Team members can instantly see the same data, at the inspection site and the office.
- Reduce the need to take notes in the field with two helpful features:
 - IR-PhotoNotes™ annotation system—captures digital images of the surrounding area to reference conditions or actual location
- Any additional details can also be saved to the file with voice annotation
- Highlight areas that are outside your pre-set 'normal' temperature ranges quickly with color alarms
- See the details you need with interchangeable smart lenses—2x and 4x telephoto and wide angle—no calibration required
- Included Fluke Connect* SmartView* desktop software: Optimize
 thermal images, perform analytics, generate quick, customizable,
 robust reports and export images to the format of your choice in
 the cloud







Powerful, new, easy-to-use Fluke Connect® SmartView® desktop software.

Now available, a comprehensive and connected software platform that represents the future of integrated equipment maintenance, monitoring, analysis and reporting. It's easier than ever to optimize thermal images, perform analytics, generate quick, customizable, robust reports, and export images to the format of your choice in the cloud. And you will be able to integrate with Fluke Connect—the largest integrated system of maintenance software and tools in the world.

- Modern visual design
- · Intuitive navigation-easier to learn, easier and faster to work in
- Simplified work flows
- Simplified reporting workflow and better report templates
- · Fluke Connect Cloud storage

Fluke Connect SmartView® desktop software is included with your camera purchase.

Download at fluke.com/FlukeConnectTI

100 % Focused-Every object. Near and far. MultiSharp™ Focus.







MultiSharp Focus, available on the Ti450.



Detailed specifications

	Ti480	Ti450	Ti400	Ti300	
Key features					
Detector resolution	640 x 480 (307,200) or 1280 x 960 with SuperResolution	320 x 240 (76,800 pixels) or 640 x 480 with SuperResolution	320 x 240 (76,800 pixels)	240 x 180 (43,200 pixels)	
SuperResolution	Yes, on camera and in software. Captures and combines 4x the data to create a 1280 x 960 image	Yes, on camera and in software. Captures and combines 4x the data to create a 640 x 480 image	-	_	
IFOV with standard lens (spatial resolution)	0.93 mRad, D:S 1065:1	1.31 mRad	, D:S 753:1	1.75 mRad, D:S 565:1	
Field of view	34 °H x 24 °V 24 °H x 17 °V				
Minimum focus distance	15 cm (approx. 6 in)				
IR-Fusion* technology	Full screen				
MultiSharp™ Focus	Yes, focused near and far,	throughout the field of view	-	-	
LaserSharp® Auto Focus	Yes, for consistently in-focus images. Every. Single. Time.				
Laser distance meter	Yes, calculates distance to the target for precisely focused images and displays distance on screen				
Advanced manual focus	Yes				
Wireless connectivity	Yes, to PC, iPhone∗ and iPad* (iOS 4s and later), Android™ 4.3 and up, and WiFi to LAN (where available)				
Fluke Connect* app compatible	Yes*, connect your camera to your smartphone, and images taken automatically upload to the Fluke Connect app for saving and sharing				
Fluke Connect* Assets optional software	Yes*, assign images to assets and create work orders. Easily compare measurement types in one location.				
Fluke Connect* Instant Upload	Yes*, connect your camera to your building's WiFi network, and images taken automatically upload to the Fluke Connect system for viewing on your smartphone or PC				
Fluke Connect* tool compatible	Yes*, connects wirelessly to select Fluke Connect enabled tools and displays measurements on camera screen.				
IR-Fusion: technology		Yes, adds the context of the visib	le details to your infrared image		
AutoBlend™ mode	Min, Mid, Max IR plus full visible on camera; continously variable in software				
Picture-In-Picture (PIP)	Yes				
Ruggedized touchscreen display		3.5 inch (landscap	oe) 640 x 480 LCD		
Rugged, ergonomic design for one-handed use	Yes				
Thermal sensitivity (NETD)**	≤ 0.05 °C at 30 °C target temp (50 mK)	≤ 0.03 °C at 30 °C target temp (30 mK)	≤ 0.05 °C at 30 °C t	target temp (50 mK)	
Level and span	Smooth auto and manual scaling				
Fast auto toggle between manual and auto modes	Yes				
Fast auto-rescale in manual mode	Yes				
Minimum span (in manual mode)	2.0 °C (3.6 °F)				
Minimum span (in auto mode)	3.0 °C (5.4 °F)				
Built-in digital camera (visible light)	5MP				
Frame rate	60 Hz or 9 Hz versions				
Laser pointer	Yes				
LED light (torch)	Yes				
Digital zoom	2x a	nd 4x		_	
Data storage and image capture					
Extensive memory options	Removable 4 GB micro SD memory card, 4 GB internal flash memory, save to USB flash drive capability, upload to Fluke Cloud™ for permanent storage				
Image capture, review, save mechanism	One-handed image capture, review, and save capability				

^{*}Fluke Connect SmartView* analysis and reporting software is available in all countries but Fluke Connect is not. Please check availability with your authorized Fluke distributor.
** Best possible



Detailed specifications

Image file formats Memory review Software Export file formats with Fluke Connect® desktop software Voice annotation IR-PhotoNotes™		non-radiometric (.b.	ometric (.is2); no analysis software mp, .jpg and .avi) files	required for	
Software Export file formats with Fluke Connect® desktop software Voice annotation	Fluke Connect deskto	Thumbnail and			
Export file formats with Fluke Connect® desktop oftware Joice annotation	Fluke Connect deskto	THAIDHAH ANA	full screen review		
oftware Joice annotation		p software—full analysis and rep	orting software with access to the	Fluke Connect system	
	Bitmap (.bmp), GIF, JPEG, PNG, TIFF				
R_PhotoNotestM	60 seconds maximum recording time per image; reviewable playback on camera, optional bluetooth headset available but not required				
It I Hotowotca	Yes (5 images)				
'ext annotation	Yes				
lideo recording	Standard and radiometric				
le formats video	Non-radiometric (MPEG - encoded .AVI) and fully-radiometric (.IS3)				
Remote display viewing	Yes, see the live stream of the camera display on your PC, smartphone, or TV monitor. Via USB, WiFi hotspot, or WiFi network to Fluke Connect software on a PC; via WiFi hotspot to the Fluke Connect® app on a smartphone; or via HDMI to a TV monitor				
Remote control operation	Yes, through Fluke Connect SmartView® desktop software or Fluke Connect mobile app				
Auto capture (temperature and interval)		7	/es		
Sattery					
Batteries (field-replaceable, rechargeable)	Two lithiu	m ion smart battery packs with fi	ve-segment LED display to show c	narge level	
Battery life	2-3 hours per battery (*Actual life varies depending on settings and usage)	3-4 hours per batte	ry (*Actual life varies depending o	1 settings and usage)	
Battery charge time	2.5 hours to full charge				
lattery charging system	Two-bay battery charger or in-imager charging. Optional 12 V automotive charging adapter				
AC operation	AC operation with included power supply (100 V AC to 240 V AC, 50/60 Hz)				
Power saving	User selectable sleep and power off modes				
Cemperature measurement					
emperature measurement range not calibrated below -10 °C)	≤ -20 °C to +800 °C (-4 °F to 1472 °F)	-20 °C to +1200 °C	C (-4 °F to +2192 °F)	-20 °C to +650 °C (-4 °F to +1202 °F)	
ccuracy	± 2 °C or 2 % (at 25 °C nominal, whichever is greater)				
n-screen emissivity correction	Yes (both value and table)				
n-screen reflected background temperature ompensation		7	/es		
n-screen transmission correction		Ţ	/es		
ive line marker	Ye	es			
Color palettes					
Standard palettes	8: Ironbow, Blue-	-Red, High Contrast, Amber, Amb	er Inverted, Hot Metal, Grayscale, G	rayscale Inverted	
Jltra Contrast™ palettes	8: Ironbow Ultra, Blue-Red Ultra		a, Amber Inverted Ultra, Hot Metal ed Ultra	Ultra, Grayscale Ultra, Graysca	
General specifications					
Color alarms (temperature alarms)		High temperature, low temperat	ure, and isotherms (within range)		
nfrared spectral band	7.5 μm to 14 μm (long wave)				
perating temperature	-10 °C to +50 °C (14 °F to 122 °F)				
Storage temperature	-20 °C to +50 °C (-4 °F to 122 °F) without batteries				
Relative humidity	10 % to 95 % non-condensing				
Center-point temperature measurement	Yes				
pot temperature	Hot and cold spot markers				
Jser-definable spot markers	3 user-definable spot markers				
Center box	Expandable-contractible measurement box with MIN-MAX-AVG temp display				
Safety	IEC 61010-1: Overvoltage category II, Pollution Degree 2				
Electromagnetic compatibility	IEC 61326-1: Basic EM environment. CISPR 11: Group 1, Class A				
Australian RCM	IEC 61326-1				
JS FCC	CFR 47, Part 15 Subpart B				
/ibration	0.03 g2/Hz (3.8 g), 2.5 g IEC 68-2-6				
Shock	25 g, IEC 68-2-29				
Orop	Engineered to withstand 2 meter (6.5 feet) drop with standard lens				
Size (H x W x L)	27.7 cm x 12.2 cm x 16.7 cm (10.9 in x 4.8 in x 6.5 in)				
Neight (battery included)	1.04 kg (2.3 lb)				
Enclosure rating	IEC 60529: IP54 (protected against dust, limited ingress; protection against water spray from all directions)				
Narranty	Two-years (standard), extended warranties are available				
Recommended calibration cycle		Two-years (assumes norma	l operation and normal aging)		
Supported languages	Czech, Dutch, English, Finnis		alian, Japanese, Korean, Polish, Po raditional Chinese, and Turkish	rtuguese, Russian, Simplified	

Ordering information

FLK-Ti480 60 Hz Thermal Imager FLK-Ti480 9 Hz Thermal Imager FLK-Ti450 60 Hz Thermal Imager FLK-Ti450 9 Hz Thermal Imager FLK-Ti400 60 Hz Thermal Imager FLK-Ti300 60 Hz Thermal Imager FLK-Ti300 9 Hz Thermal Imager

Included

Thermal imager with standard infrared lens; AC power supply and battery pack charger (including universal AC adapters); two rugged lithium ion smart battery packs; USB cable; HDMI video cable; 4 GB micro SD card; rugged, hard carrying case; soft transport bag and adjustable hand strap. Available by free download: Fluke Connect* SmartView* desktop software and user manual.

Optional accessories

FLK-LENS/TELE2 Infrared Telephoto Lens (2X magnification), Ti480, Ti450, Ti400, Ti300
FLK-LENS/4XTELE2 Infrared Telephoto Lens (4X magnification), Ti450, Ti400, Ti300
FLK-LENS/WIDE2 Infrared Wide Angle Lens, Ti480, Ti450, Ti400, Ti300

TI-CAR-CHARGER Car Charger FLK-TI-VISOR3 Sun Visor

BOOK-ITP Introduction to Thermography Principles Book **TI-TRIPOD3** Tripod Mounting Accessory

FLK-TI-BLUETOOTH Bluetooth headset

FLK-TI-SBP3 Additional Smart Battery

FLK-TI-SBC3B Additional Smart Battery Charger

Kits

FLK-T1400 60HZ/FCA* Thermal Imager, 3000 FC DMM, a3001FC iFlex Module

FLK-TI300 60HZ/FCA* Thermal Imager, 3000 FC DMM, a3001FC iFlex Module

FLK-T1400 60HZ/FCC* Thermal Imager, 3-a3001FC iFlex Modules, 805 Vibration Tester

FLK-T1400 9HZ/FCA Thermal Imager, 3000 FC DMM, a3001FC iFlex Module

FLK-TI300 9HZ/FCA Thermal Imager, 3000 FC DMM, a3001FC iFlex Module

FLK-T1400 9HZ/FCC Thermal Imager, 3-a3001FC iFlex Modules, 805 Vibration Tester

Visit www.fluke.com to get complete details on these products or ask your local Fluke sales representative.

*Only available in certain countries.

RF connection time (binding time) may take up to 1 minute.

The Expert Series

Go expert with the Fluke TIX580, TiX560, TiX520 or TiX500, and get up to 640 x 480 resolution along with maximum flexibility of a screen that rotates a full 240 degrees and a 5.7 inch touchscreen LCD. Includes in-field analysis and post-capture image processing on camera, along with other expert-level features and more lens options.





Preventive maintenance simplified. Rework eliminated.

Save time and improve the reliability of your maintenance data by wirelessly syncing measurements using the Fluke Connect* system.

- Eliminate data-entry errors by saving measurements directly from the tool and associating them with the work order, report or asset record.
- Maximize uptime and make confident maintenance decisions with data you can trust and trace.
- Move away from clipboards, notebooks and multiple spreadsheets with a wireless one-step measurement transfer.
- · Access baseline, historical and current measurements by asset.
- Share your measurement data using ShareLive™ video calls and emails.
- The Ti4XX Series and Ti300 is part of a growing system of connected test tools and equipment maintenance software. Visit the website to learn more about the Fluke Connect* system.

Find out more at flukeconnect.com







All trademarks are the property of their respective owners. WiFi or cellular service required to share data. Smartphone, wireless service and data plan not included with purchase. First 5 GB of storage is free. Phone support details can be viewed at fluke.com/phones.

Smart phone wireless service and data plan not included with purchase. Fluke Connect is not available in all countries.

Fluke. Keeping your world up and running.®

Fluke Europe B.V.

P.O. Box 1186 5602 BD Eindhoven The Netherlands Web: www.fluke.co.uk

For more information call:

In Europe/M-East/Africa +31 (0)40 267 5100 or Fax +31 (0)40 267 5222

Fluke (UK) Ltd.

52 Hurricane Way Norwich, Norfolk NR6 6JB United Kingdom

Tel.: +44 (Ō) 20 7942 0700 Fax: +44 (O) 20 7942 0701 E-mail: industrial@uk.fluke.nl Web: www.fluke.co.uk

© 2016 Fluke Corporation. All rights reserved. Data subject to alteration without notice. $11/2016\ 6002304$ l-uken

Modification of this document is not permitted without written permission from Fluke Corporation.