

Supplement

Manual Title:	i3000s/i2000s Flex Instruction Sheet		
Part Number:	2560447	Supplement Issue:	3
Print Date:	March 2006	Issue Date:	8/19
Revision/Date:	1, 4/17	Page Count:	1

This supplement contains information necessary to ensure the accuracy of the above manual.

Change #1, 451, 598

Under the **Specifications, Electrical Characteristics** section, replace Operating temperature and Storage temperature with:

Operating temperature: -20 °C to +50 °C

Storage temperature: -20 °C to +60 °C (without batteries)

Under **Measuring Head Characteristics** remove the Operating temperature and Storage temperature.

Change #2, 739, 744

On the 4th page, replace the Position sensitivity and add the figure and the text:

Position sensitivity From 1 % up to 3 % of range with cable, depending on distance from the center (see diagram below). Measurements closer than 25 mm from the coupling are typically greater than 3 % of range.

External Wire influence: 1 % (-40 db) of external current >200 mm from head.

